

品番	砥材	粒度	硬度	結合剤	形状	寸法(mm)		周速度 m/s	入数(枚)
						外径×厚み×穴径			
1000E20460	CX	60	I	V	1	205×19×31.75	40	3	
1000E20470	CX	60	J	V	1	205×19×31.75	40	3	
1000E20480	CX	80	J	V	1	205×19×31.75	40	3	
※ 1000E20490	CX	120	J	V	1	205×19×31.75	40	3	
1000E20500	CX	46	I	V	1	205×19×50.8	40	3	
1000E20510	CX	46	J	V	1	205×19×50.8	40	3	
◎ 1000E20520	CX	60	F	V	1	205×19×50.8	40	3	
1000E20530	CX	60	H	V	1	205×19×50.8	40	3	
1000E20540	CX	60	J	V	1	205×19×50.8	40	3	
1000E20550	CX	80	I	V	1	205×19×50.8	40	3	
1000E20560	CX	80	J	V	1	205×19×50.8	40	3	
1000E20650	CXY	60	H	V	1	255×25×50.8	40	3	
1000E20660	CXY	60	J	V	1	255×25×50.8	40	3	
1000E20670	CXY	80	J	V	1	255×25×76.2	40	3	
1000E20680	CXY	46	H	V	1	305×25×76.2	40	2	
1000E20690	CXY	46	J	V	1	305×25×76.2	40	2	
1000E20700	CXY	60	H	V	1	305×25×76.2	40	2	
1000E20710	CXY	60	J	V	1	305×25×76.2	40	2	
1000E20720	CXY	60	J	V	1	305×25×127	40	2	
1000E20730	CXY	80	K	V	1	305×25×127	40	2	
1000E20740	CXY	46	H	V	1	305×32×76.2	40	2	
1000E21510	CXY	46	I	V	1	305×32×76.2	40	2	
1000E20750	CXY	46	J	V	1	305×32×76.2	40	2	
1000E20760	CXY	60	H	V	1	305×32×76.2	40	2	
1000E21520	CXY	60	I	V	1	305×32×76.2	40	2	
1000E20770	CXY	60	J	V	1	305×32×76.2	40	2	
※ 1000E21530	CXY	80	I	V	1	305×32×76.2	40	2	
1000E20780	CXY	80	J	V	1	305×32×76.2	40	2	
※ 1000E20790	CXY	46	H	V	1	305×32×127	40	2	
※ 1000E20800	CXY	46	J	V	1	305×32×127	40	2	
1000E20810	CXY	60	J	V	1	305×32×127	40	2	
1000E20820	CXY	80	J	V	1	305×32×127	40	2	
1000E20830	CXY	46	H	V	1	305×38×76.2	40	2	
1000E20840	CXY	46	J	V	1	305×38×76.2	40	2	
1000E20850	CXY	60	H	V	1	305×38×76.2	40	2	
1000E20860	CXY	60	J	V	1	305×38×76.2	40	2	
1000E20870	CXY	46	H	V	1	305×38×127	40	2	
1000E21540	CXY	46	I	V	1	305×38×127	40	2	
1000E20880	CXY	46	J	V	1	305×38×127	40	2	
1000E20890	CXY	60	H	V	1	305×38×127	40	2	
1000E21550	CXY	60	I	V	1	305×38×127	40	2	
1000E20900	CXY	60	J	V	1	305×38×127	40	2	
※ 1000E21560	CXY	80	I	V	1	305×38×127	40	2	
1000E20910	CXY	80	J	V	1	305×38×127	40	2	
1000E20920	CXY	60	J	V	1	305×50×127	40	1	

品番	砥材	粒度	硬度	結合剤	形状	寸法(mm)		周速度 m/s	入数(枚)
						外径×厚み×穴径			
1000E20930	CXY	60	J	V	1	355×25×127	40	1	
1000E20940	CXY	80	K	V	1	355×25×127	40	1	
1000E20950	CXY	60	H	V	1	355×32×76.2	40	1	
1000E20960	CXY	46	J	V	1	355×32×127	40	1	
1000E20970	CXY	60	J	V	1	355×32×127	40	1	
※ 1000E20980	CXY	60	K	V	1	355×32×127	40	1	
1000E20990	CXY	80	J	V	1	355×32×127	40	1	
※ 1000E21000	CXY	80	K	V	1	355×32×127	40	1	
1000E21010	CXY	46	H	V	1	355×38×76.2	40	1	
1000E21020	CXY	46	J	V	1	355×38×76.2	40	1	
1000E21030	CXY	46	H	V	1	355×38×127	40	1	
1000E21570	CXY	46	I	V	1	355×38×127	40	1	
1000E21040	CXY	46	J	V	1	355×38×127	40	1	
1000E21050	CXY	60	H	V	1	355×38×127	40	1	
1000E21580	CXY	60	I	V	1	355×38×127	40	1	
1000E21060	CXY	60	J	V	1	355×38×127	40	1	
※ 1000E21070	CXY	60	K	V	1	355×38×127	40	1	
1000E21080	CXY	80	J	V	1	355×38×127	40	1	
1000E21090	CXY	80	K	V	1	355×38×127	40	1	
1000E21590	CXY	46	H	V	1	355×50×127	40	1	
1000E21100	CXY	46	J	V	1	355×50×127	40	1	
1000E21110	CXY	60	H	V	1	355×50×127	40	1	
1000E21120	CXY	60	J	V	1	355×50×127	40	1	
1000E21130	CXY	60	K	V	1	355×50×127	40	1	
1000E21600	CXY	80	J	V	1	355×50×127	40	1	
1000E21140	CXY	80	K	V	1	355×50×127	40	1	
1000E21150	CXY	80	K	V	1	405×25×127	40	1	
※ 1000E21160	CXY	80	K	V	1	405×25×152.4	40	1	
1000E21170	CXY	80	K	V	1	405×32×127	40	1	
1000E21180	CXY	60	K	V	1	405×38×127	40	1	
1000E21610	CXY	80	K	V	1	405×38×127	40	1	
1000E21190	CXY	80	K	V	1	405×38×152.4	40	1	
※ 1000E21200	CXY	60	K	V	1	405×38×203.2	40	1	
※ 1000E21210	CXY	80	K	V	1	405×38×203.2	40	1	
※ 1000E21620	CXY	46	H	V	1	405×50×127	40	1	
1000E21220	CXY	46	J	V	1	405×50×127	40	1	
※ 1000E21230	CXY	60	H	V	1	405×50×127	40	1	
1000E21630	CXY	60	J	V	1	405×50×127	40	1	
1000E21240	CXY	60	K	V	1	405×50×127	40	1	
1000E21640	CXY	80	J	V	1	405×50×127	40	1	
1000E21250	CXY	80	K	V	1	405×50×127	40	1	
1000E21260	CXY	60	K	V	1	405×50×152.4	40	1	
1000E21270	CXY	80	K	V	1	405×50×152.4	40	1	
1000E21650	CXY	46	H	V	1	510×50×127	40	1	
※ 1000E21660	CXY	46	I	V	1	510×50×127	40	1	

切断砥石

オフセット砥石

ビットフライド砥石

ビットホイール

ダイヤモンド工具

ドレッシング工具

周辺機器

研削油

フリップディスク

研磨材

選定表

技術資料