

F1

Threaded Type
Flexible Hose

NK-1000 Standard Union Type (Female Both Ends)

DN: 8mm(1/4") ~ 65mm(2-1/2")

Length: 200mm ~ 10M

*For any other specifications, please contact us.



① Tube	Stainless Steel
② Braid	Stainless Steel
③ Union	Carbon steel, Stainless Steel, Copper Alloy
④ Collar	Stainless Steel
⑤ Gasket	Non Asbestos

NK-1100 Fit Union Type (Female Both Ends)

DN: 10mm(3/8") ~ 50mm(2")

Length: 200mm ~ 3M

*For any other specifications, please contact us.



① Tube	Stainless Steel
② Braid	Stainless Steel
③ Union	Carbon Steel, Stainless Steel, Copper Alloy
④ Ring	Carbon Steel, Stainless Steel
⑤ Base Block	Carbon Steel, Stainless Steel
⑥ Gasket	Non Asbestos