

NK-5500

(Floating x Fixed Flange)

NK-5600

(Both Ends Floating Flange)

Braid-Over Type

DN: 50mm(2") ~ 350mm(14")
 Length: 300mm ~ 10M
 *For any other specifications, please contact us.
 Flange Standard: JIS, ANSI, DIN, ASME

① Tube	Stainless Steel
② Braid	Stainless Steel
③ Ring	Stainless Steel
④ Stub End	Carbon Steel, Stainless Steel
⑤ Flange	Carbon Steel, Stainless Steel
⑥ Neck Ring	Carbon Steel, Stainless Steel
⑦ End Pipe	Carbon Steel, Stainless Steel



Threaded Type Flexible Hose

F1

Flange Type Flexible Hose

F2

Fire Law Flexible Hose

NK-6300

Non Welded Type

DN: 20mm(3/4") ~ 300mm(12")
 Length: 300mm ~ 3M
 *For any other specifications, please contact us.
 Flange Standard: JIS, ANSI, DIN, ASME

① Tube	Stainless Steel
② Braid	Stainless Steel
③ Ring	Stainless Steel
④ Separate Ring	Carbon Steel, Stainless Steel
⑤ Flange	Carbon Steel, Stainless Steel
⑥ Gasket	Non Asbestos



F3

Quick Connection Flexible Hose

F4

Flexible Hose for Vacuums

NK-7800

Pump Joint Super 10・Super 20

DN: 50mm(2") ~ 300mm(12")
 Length: Depending on the DN.
 Flange Standard: JIS, ANSI, DIN, ASME

Super 10		Super 20	
DN (mm)	Length (mm)	DN (mm)	Length (mm)
50	150	50	110
65	150	65	110
80	150	80	110
100	150	100	150
125	150	125	150
150	150	150	150
200	200	200	200
250	200	250	200
300	200	300	200

① 2 ply Bellows	Stainless Steel
② Flange	Carbon Steel, Stainless Steel
③ Holder	Carbon Steel, Stainless Steel
④ Tierod	Carbon Steel, Stainless Steel
⑤ Cushion	Urethane
⑥ Adjust Nut	Carbon Steel, Stainless Steel



F5

Flexible Hose with Fluororesin

F6

Other Flexible Hose

F7