

NK-1400 Pipe End Type

This product is used for budd welding.



① Tube	Stainless Steel
② Braid	Stainless Steel
③ Ring	Stainless Steel
④ Pipe	Carbon Steel, Stainless Steel, Copper Alloy

Threaded Type Flexible Hose

F1

Flange Type Flexible Hose

F2

Fire Law Flexible Hose

NK-HPG KHKS0803 Type (for high Pressure Gas)

High Pressure Gas Safety Act is a Japanese law to protect public safety. There are some types like inflammable gas and toxicity gas. This product has good intensity and endurance, and it can correspond to this law.

- NK-HPG-F : Flange Type
- NK-HPG-S : Thread Type
- NK-HPG-P : Pipe End Type



① Fitting	Carbon Steel, Stainless Steel
② End Pipe	Carbon Steel, Stainless Steel
③ Socket(only for NFK-HPG-F)	Carbon Steel, Stainless Steel
④ Ring	Stainless Steel
⑤ Tube	Stainless Steel
⑥ Braid	Stainless Steel

F3

Quick Connection Flexible Hose

F4

Flexible Hose for Vacuums

NK-JLP JLPA209-2010 Type (for LPG)

a) Union Type DN: 15mm(1/2") ~ 20mm(3/4")

① Tube	Stainless Steel
② Braid	Stainless Steel
③ Ring	Stainless Steel
④ Union	Stainless Steel
⑤ Gasket	Non Asbestos

b) Flange Type DN: 15mm(1/2") ~ 100mm(4")

① Tube	Stainless Steel
② Braid	Stainless Steel
③ Ring	Stainless Steel
④ Stub End	Carbon Steel, Stainless Steel
⑤ Floating Flange	Carbon Steel, Stainless Steel
⑥ End Pipe	Carbon Steel, Stainless Steel
⑦ Fixed Flange	Carbon Steel, Stainless Steel



Flexible Hose with Fluororesin

F6

Other Flexible Hose

F7