



BN-3R01(3R01H1)

8A・10A・15A・20A・25A




*圧力計・ブラケットはオプションです。圧力計の仕様は(P21)をご覧下さい。

8A




呼 径 記 号	BN-3R01(3R01H1)							BN-3R01P(パネルタイプ)						
	d	S	L	D	H1	H2	H	H2	H	G	J	K	V	
8A	Rc1/4	26	75	80	35	113	148	127	162	M24×1.5	73	9	6	
10A	Rc3/8													
15A	Rc1/2	36	80	86	39	122	161	136	175	M30×1.5	82	9	6	
20A	Rc3/4	46	90	100	48	138	186	150	198		92	10	7	
25A	Rc1													


10A




15A



20A





25A



BN-3R21

8A



*圧力計・ブラケットはオプションです。圧力計の仕様は(P21)をご覧下さい。