

TOMBO No.9003 ナフロン[®] PTFEチューブ

(ミリサイズ)

呼び寸法 (mm)		内径 (mm)		肉厚 (mm)		長さ (m)		呼び寸法 (mm)		内径 (mm)		肉厚 (mm)		長さ (m)	
内径×外径	基準寸法	許容差	基準寸法	許容差	基準寸法	許容差		内径×外径	基準寸法	許容差	基準寸法	許容差	基準寸法	許容差	
0.5× 1.5	0.5	+0.30	0.5					14.0×16.0	14.0	±0.50	1.0	+0.13 -0.10			
1.0× 2.0	1.0	-0.10	0.5					15.0×17.0	15.0		1.5	+0.13 -0.10			
1.0× 3.0	1.0		1.0					16.0×17.5	16.0		0.75	+0.13 -0.10	10		
2.0× 3.0	2.0	+0.50	0.5					16.0×18.0	16.0	±0.60	1.0	+0.13 -0.10			
2.0× 4.0	2.0	-0.20	1.0					16.0×19.0	16.0		1.5	±0.18			
3.0× 4.0	3.0		0.5					19.0×21.0	19.0		1.0	+0.13 -0.10			
3.0× 5.0	3.0		1.0					20.0×23.0	20.0		1.5	±0.18			
4.0× 5.0	4.0		0.5					21.5×23.5	21.5		1.0	+0.13			
4.0× 6.0	4.0		1.0	+0.13				22.0×24.0	22.0		1.0	-0.10			
5.0× 6.0	5.0		0.5	-0.10				23.0×25.0	23.0		1.0				
5.0× 7.0	5.0		1.0					23.0×27.0	23.0	±0.70	2.0	±0.28			
6.0× 7.0	6.0		0.5					25.0×27.0	25.0		1.0	+0.13 -0.10			
6.0× 8.0	6.0		1.0					25.0×28.0	25.0		1.5	±0.18			
7.0× 8.0	7.0	+0.50	0.5					26.0×29.0	26.0		1.5	±0.18	1, 5		
7.0× 9.0	7.0	-0.40	1.0					27.5×29.5	27.5	±0.80	1.0	+0.13 -0.10			
8.0× 9.0	8.0		0.5					33.0×36.0	33.0	±1.00	1.5	±0.18			
8.0×10.0	8.0		1.0					39.0×42.0	39.0		1.5	±0.18			
9.0×10.0	9.0		0.5					46.0×50.0	46.0	±1.50	2.0				
9.0×11.0	9.0		1.0					49.0×53.0	49.0		2.0				
9.0×12.0	9.0		1.5	±0.18				64.0×68.0	64.0	±2.00	2.0	±0.28			
10.0×11.0	10.0		0.5					76.0×80.0	76.0	±2.50	2.0				
10.0×12.0	10.0		1.0												
11.0×12.0	11.0		0.5												
11.0×13.0	11.0		1.0	+0.13											
12.0×13.0	12.0		0.5	-0.10											
12.0×14.0	12.0		1.0												
12.5×14.0	12.5	±0.50	0.75												
13.0×15.0	13.0		1.0												
13.0×16.0	13.0		1.5	±0.18											

※納期 (在庫の有無) についてはご確認ください。

(インチサイズ)

呼び寸法 (mm)		内径 (mm)		肉厚 (mm)		長さ (m)	
内径×外径	基準寸法	許容差	基準寸法	許容差	基準寸法	許容差	
1.59× 3.17	1.59	+0.50 -0.20	0.79	+0.13 -0.10			
3.17× 6.35	3.17		1.59	±0.18			
4.35× 6.35	4.35		1.00	+0.13 -0.10	10,		
6.35× 9.52	6.35	+0.50 -0.40	1.59	±0.18	20,	+2%	
7.52× 9.52	7.52		1.00	+0.13 -0.10	30,	-0	
9.52× 12.70	9.52		1.59	±0.18	50		
10.70× 12.70	10.70	±0.50	1.00	+0.13 -0.10			
15.88× 19.05	15.88	±0.60	1.59	±0.18			

※納期 (在庫の有無) についてはご確認ください。