










Accessories (Collet, etc.)

Collet	Code No.	Model	I.D.	Compatible model		
 <p>※CH16-10.0 Length 24.5 Collet CH16 Group</p>	93130	CH16-3.0	ø3.0	BMS-4020·BMS-4040 BMS-4020 2M·BMS-4040 2M BMS-4020RA·BMS-4040RA·NR-4040 QC5-16 (NRR4040-QC) QC5-16 (NR4040-AQC) BMS-4040-RGD-03M BMS-4040-RGD-2M BMS-4040RA-RGD-03M BMS-4040RA-RGD-2M		
	93193	CH16-3.175	ø3.175			
	93140	CH16-4.0	ø4.0			
	93160	CH16-6.0	ø6.0			
	93196	CH16-6.35	ø6.35			
	93180	CH16-8.0	ø8.0			
	93100	CH16-10.0	ø10.0			
	 <p>※CH16OH-9.0, 10.0 Length 24.5 Collet CH16OH Group</p>	93330	CH16OH-3.0		ø3.0	BMS-4020-MQL BMS-4040-MQL BMS-4020-MQL-2M BMS-4040-MQL-2M
		93331	CH16OH-3.175		ø3.175	
		93340	CH16OH-4.0		ø4.0	
93350		CH16OH-5.0	ø5.0			
93360		CH16OH-6.0	ø6.0			
93363		CH16OH-6.35	ø6.35			
93370		CH16OH-7.0	ø7.0			
93380		CH16OH-8.0	ø8.0			
93390		CH16OH-9.0	ø9.0			
93400		CH16OH-10.0	ø10.0			
 <p>ø1.0 ~ ø6.35</p>  <p>ø0.5 ~ ø0.9</p> <p>Collet CHK Group</p>	91597	CHK-3.0AA	ø3.0AA※	QC5-K (NRR4040-QC) QC5-K (NR4040-AQC) ※ High precision type AA (Run-out Accuracy within 2 μm)		
	91598	CHK-3.175AA	ø3.175AA※			
	91599	CHK-4.0AA	ø4.0AA※			
	91600	CHK-6.0AA	ø6.0AA※			
	91601	CHK-6.35AA	ø6.35AA※			
	91592	CHK-2.35	ø2.35			
	91530	CHK-3.0	ø3.0			
	91593	CHK-3.175	ø3.175			
	91540	CHK-4.0	ø4.0			
	91560	CHK-6.0	ø6.0			
	91596	CHK-6.35	ø6.35			
	—	CHK-□□	ø0.5, ø0.6, ø0.7, ø0.8, ø0.9 ø1.0, ø1.5, ø2.0, ø2.5, ø3.5, ø4.5, ø4.76, ø5.5 ø1.1, ø1.2, ø1.3, ø1.4, ø1.7, ø1.8, ø1.9, ø2.1, ø2.2, ø2.3, ø2.4, ø2.6, ø2.7, ø2.8, ø2.9, ø3.1, ø3.2, ø3.3, ø3.4, ø3.6, ø3.7, ø3.8, ø3.9, ø4.1, ø4.2, ø4.3, ø4.4, ø4.6, ø4.7, ø4.8, ø4.9, ø5.1, ø5.2, ø5.3, ø5.4, ø5.6, ø5.7, ø5.8, ø5.9 ø1.6, ø5.0			
	93630	CHK-OH-3.0	ø3.0		BMS-4020-MQL-CHK BMS-4020-MQL-CHK-2M BMS-4040-MQL-CHK BMS-4040-MQL-CHK-2M	
	93631	CHK-OH-3.175	ø3.175			
	93640	CHK-OH-4.0	ø4.0			
93650	CHK-OH-5.0	ø5.0				
93660	CHK-OH-6.0	ø6.0				
93663	CHK-OH-6.35	ø6.35				
 <p>Collet nut</p>	2161	CHN-16	Collet nut for CH16 Collet	BMS-4020·BMS-4040·BMS-4020 2M BMS-4040 2M·BMS-4020RA·BMS-4040RA NR-4040·QC5-16 (NRR4040-QC) QC5-16 (NR4040-AQC) BMS-4020-MQL·BMS-4040-MQL BMS-4020-MQL-2M·BMS-4040-MQL-2M BMS-4040-RGD-03M·BMS-4040-RGD-2M BMS-4040RA-RGD-03M BMS-4040RA-RGD-2M		
	2129	K-265	Collet nut for CHK Collet		QC5-K (NRR4040-QC) · QC5-K (NR4040-AQC) BMS-4020-MQL-CHK · BMS-4020-MQL-CHK-2M BMS-4040-MQL-CHK · BMS-4040-MQL-CHK-2M	
 <p>Collet holder</p>	9216	QC5-16	Collet holder for CH16 ※With CHN-16	NRR4040-QC NR4040-AQC		
	9225	QC5-16-R				
 <p>Collet holder</p>	9215	QC5-K	Collet holder for CHK ※With K-265	NRR4040-QC NR4040-AQC		
	9224	QC5-K-R				
 <p>Preset adapter</p>	9218	QC5-16 ADP	Preset adapter	QC5-16		
	9217	QC5-K ADP	Preset adapter	QC5-K		
 <p>Adjuster Bolt</p>	7739	ADJUSTER BOLT	Adjuster Bolt	BMS-4020-MQL-CHK BMS-4020-MQL-CHK-2M BMS-4040-MQL-CHK BMS-4040-MQL-CHK-2M		