

屋内用  
片扉 IP2XD  
両扉 IP2XC

ライトベージュ塗装  
LB色(SY71)  
日塗工F25-70B

クリーム塗装  
クリーム色(2,SY91)  
日塗工F22-90B

フカサ 140mm

単位/mm

納期区分		木製基板付		納期区分		鉄製基板付		1 コ 標準価格 円	一 梱 入 数	扉形式	外形寸法			取付基板寸法		有効フカサ		製品質量 kg	
LB色	C色	品名	記号	LB色	C色	品名	記号				ヨコ	タテ	フカサ	ヨコ	タテ	Bタイプ	Sタイプ	Bタイプ	Sタイプ
◎	◎	B14-69		◎	◎	S14-69		42,000	1	片扉	600	900	140	520	820	108	121	27.4	31.3
◎	◎	B14-610		◎	◎	S14-610		42,500	1	〃	〃	1,000	〃	〃	920	〃	115	30.1	34.5
◎	◎	B14-74-2		③	③	S14-74-2		35,500	1	両扉	700	400	140	620	320	108	121	17.3	19.2
◎	◎	B14-75-1		◎	◎	S14-75-1		34,000	1	片扉	〃	500	〃	〃	420	〃	〃	19.2	21.6
◎	◎	B14-76-1		◎	◎	S14-76-1		35,000	1	〃	〃	600	〃	〃	520	〃	〃	22.1	25.1
◎	◎	B14-77-1		◎	◎	S14-77-1		38,000	1	〃	〃	700	〃	〃	620	〃	〃	25.1	28.6
◎	◎	B14-78-1		◎	◎	S14-78-1		41,000	1	〃	〃	800	〃	〃	720	〃	〃	28.1	32.1
◎	◎	B14-79-2		◎	◎	S14-79-2		46,500	1	両扉	〃	900	〃	〃	820	〃	〃	32.5	37.1
◎	◎	B14-710-2		◎	◎	S14-710-2		53,000	1	〃	〃	1,000	〃	〃	920	〃	〃	35.9	41.0
◎	◎	B14-84-2		③	③	S14-84-2		37,500	1	両扉	800	400	140	720	320	108	121	19.3	21.5
◎	◎	B14-85-2		◎	◎	S14-85-2		40,500	1	〃	〃	500	〃	〃	420	〃	〃	22.7	25.5
◎	◎	B14-86-2		◎	◎	S14-86-2		44,500	1	〃	〃	600	〃	〃	520	〃	〃	26.1	29.5
◎	◎	B14-87-2		◎	◎	S14-87-2		45,500	1	〃	〃	700	〃	〃	620	〃	〃	29.4	33.5
◎	◎	B14-88-2		◎	◎	S14-88-2		46,500	1	〃	〃	800	〃	〃	720	〃	〃	32.8	37.5
◎	◎	B14-89-2		◎	◎	S14-89-2		52,000	1	〃	〃	900	〃	〃	820	〃	〃	36.2	41.5
◎	◎	B14-94-2		③	③	S14-94-2		40,500	1	両扉	900	400	140	820	320	108	121	21.2	23.7
◎	◎	B14-95-2		③	③	S14-95-2		44,500	1	〃	〃	500	〃	〃	420	〃	〃	25.0	28.1
◎	◎	B14-911-2		◎	◎	S14-911-2		66,500	1	〃	〃	1,100	〃	〃	1,020	〃	〃	47.8	55.2
◎	◎	B14-104-2		③	③	S14-104-2		42,500	1	両扉	1,000	400	140	920	320	108	115	23.2	25.9
◎	◎	B14-105-2		◎	◎	S14-105-2		46,500	1	〃	〃	500	〃	〃	420	〃	〃	27.3	30.8
③	③	B14-124-2		③	③	S14-124-2		48,500	1	両扉	1,200	400	140	1,120	320	108	115	27.1	30.4
◎	◎	B14-125-2		③	③	S14-125-2		50,500	1	〃	〃	500	〃	〃	420	〃	〃	31.9	36.2

★両扉の合せ部の有効フカサは上記有効フカサより23mm引いた寸法となります。

フカサ 160mm

◎	◎	B16-33		◎	◎	S16-33		11,500	2コ	片扉	300	300	160	220	220	128	141	7.1	7.6
◎	◎	B16-34		◎	◎	S16-34		14,500	2コ	〃	〃	400	〃	〃	320	〃	〃	8.7	9.5
◎	◎	B16-345		◎	◎	S16-345		14,500	1コ	〃	〃	450	〃	〃	370	〃	〃	9.6	10.4
◎	◎	B16-35		◎	◎	S16-35		17,500	1コ	〃	〃	500	〃	〃	420	〃	〃	10.4	11.3
◎	◎	B16-36		◎	◎	S16-36		19,500	1コ	〃	〃	600	〃	〃	520	〃	〃	12.0	13.2
◎	◎	B16-3510		◎	③	S16-3510		37,000	1コ	片扉	350	1,000	160	270	920	128	135	20.7	23.1
③	③	B16-3511		③	③	S16-3511		39,000	1コ	〃	〃	1,100	〃	〃	1,020	〃	〃	22.5	25.1
③	③	B16-3512		③	③	S16-3512		41,000	1コ	〃	〃	1,200	〃	〃	1,120	〃	〃	24.3	27.2
③	③	B16-3513		③	③	S16-3513		42,500	1コ	〃	〃	1,300	〃	〃	1,220	〃	〃	26.1	29.3
③	③	B16-3514		③	③	S16-3514		46,500	1コ	〃	〃	1,400	〃	〃	1,320	〃	〃	30.6	33.9
◎	③	B16-3516		③	③	S16-3516		50,500	1コ	〃	〃	1,600	〃	〃	1,520	〃	〃	34.5	38.3
◎	◎	B16-43		◎	◎	S16-43		14,500	2コ	片扉	400	300	160	320	220	128	141	8.8	9.5
◎	◎	B16-44		◎	◎	S16-44		18,500	1コ	〃	〃	400	〃	〃	320	〃	〃	10.7	11.8
◎	◎	B16-45		◎	◎	S16-45		21,500	1コ	〃	〃	500	〃	〃	420	〃	〃	12.7	14.0
◎	◎	B16-46		◎	◎	S16-46		26,000	1コ	〃	〃	600	〃	〃	520	〃	〃	14.7	16.3
◎	◎	B16-47		◎	◎	S16-47		30,000	1コ	〃	〃	700	〃	〃	620	〃	〃	16.7	18.6
◎	◎	B16-48		◎	◎	S16-48		35,000	1コ	〃	〃	800	〃	〃	720	〃	〃	18.7	20.9
◎	◎	B16-410		◎	◎	S16-410		41,000	1コ	〃	〃	1,000	〃	〃	920	〃	135	22.8	25.5
◎	◎	B16-412		③	③	S16-412		44,500	1コ	〃	〃	1,200	〃	〃	1,120	〃	〃	26.7	30.1
◎	◎	B16-53		◎	◎	S16-53		19,500	1コ	片扉	500	300	160	420	220	128	141	10.4	11.3
◎	◎	B16-54		◎	◎	S16-54		21,500	1コ	〃	〃	400	〃	〃	320	〃	〃	12.8	14.1
◎	◎	B16-55		◎	◎	S16-55		26,000	1コ	〃	〃	500	〃	〃	420	〃	〃	15.1	16.8
◎	◎	B16-56		◎	◎	S16-56		28,000	1コ	〃	〃	600	〃	〃	520	〃	〃	17.4	19.5
◎	◎	B16-57		◎	◎	S16-57		32,000	1コ	〃	〃	700	〃	〃	620	〃	〃	19.7	22.2
◎	◎	B16-58		◎	◎	S16-58		37,000	1コ	〃	〃	800	〃	〃	720	〃	〃	22.1	24.9
◎	◎	B16-59		◎	◎	S16-59		41,000	1コ	〃	〃	900	〃	〃	820	〃	〃	24.4	27.6

◎代理店様在庫品 ◎物流センター在庫品 ①③⑤⑦標準品(納期別) (受)受注品

上記品名記号はライトベージュ塗装です。  
クリーム塗装にてご注文の際は品名記号の末尾にCを付けてご用命ください。  
価格は同価格です。[例]B14-69→B14-69Cとなります。