

屋内用
片扉 IP2XD
両扉 IP2XC

ライトベージュ塗装
LB色(5Y7.1)
白塗工F25-70B

クリーム塗装
クリーム色(2.5Y9.1)
白塗工F22-90B

フカサ 160mm

単位/mm

納期区分		木製基板付		納期区分		鉄製基板付		標準価格 円	一梱 入数	扉形式	外形寸法			取付基板寸法		有効フカサ		製品質量 kg	
LB色	C色	品名	記号	LB色	C色	品名	記号				ヨコ	タテ	フカサ	ヨコ	タテ	Bタイプ	Sタイプ	Bタイプ	Sタイプ
◎	◎	B16-812-1		◎	◎	S16-812-1		63,000	1	片扉	800	1,200	160	720	1,120	128	141	45.9	53.1
◎	◎	B16-812-2		◎	◎	S16-812-2		66,500	1	両扉	"	"	"	"	"	"	"	47.8	54.9
◎	◎	B16-814-1		◎	◎	S16-814-1		70,000	1	片扉	"	1,400	"	"	1,320	"	"	57.6	66.0
◎	◎	B16-814-2		③	③	S16-814-2		73,500	1	両扉	"	"	"	"	"	"	"	59.7	68.1
◎	◎	B16-816-1		◎	◎	S16-816-1		82,000	1	片扉	"	1,600	"	"	1,520	"	"	65.0	74.6
◎	◎	B16-816-2		③	③	S16-816-2		85,500	1	両扉	"	"	"	"	"	"	"	67.2	76.8
◎	◎	B16-94-2		③	③	S16-94-2		40,500	1	両扉	900	400	160	820	320	128	141	21.9	24.4
◎	◎	B16-95-2		◎	◎	S16-95-2		42,500	1	"	"	500	"	"	420	"	"	25.7	28.9
◎	◎	B16-104-2		③	③	S16-104-2		50,500	1	両扉	1,000	400	160	920	320	128	135	23.9	26.7
◎	◎	B16-105-2		◎	◎	S16-105-2		52,000	1	"	"	500	"	"	420	"	"	28.0	31.6
◎	◎	B16-106-2		◎	◎	S16-106-2		54,000	1	"	"	600	"	"	520	"	"	32.2	36.5
◎	◎	B16-107-2		◎	◎	S16-107-2		56,000	1	"	"	700	"	"	620	"	"	36.3	41.4
◎	◎	B16-108-2		◎	◎	S16-108-2		58,500	1	"	"	800	"	"	720	"	"	40.4	46.3
◎	◎	B16-109-2		◎	◎	S16-109-2		66,500	1	"	"	900	"	"	820	"	"	44.6	51.3
◎	◎	B16-1010-2		◎	◎	S16-1010-2		68,500	1	"	"	1,000	"	"	920	"	"	49.1	57.1
◎	◎	B16-1011-2		◎	◎	S16-1011-2		70,000	1	"	"	1,100	"	"	1,020	"	"	53.2	62.1
◎	◎	B16-1012-2		◎	◎	S16-1012-2		72,000	1	"	"	1,200	"	"	1,120	"	"	57.4	67.0
◎	◎	B16-1014-2		◎	◎	S16-1014-2		85,500	1	"	"	1,400	"	"	1,320	"	"	71.0	82.3
◎	◎	B16-1016-2		◎	◎	S16-1016-2		104,000	1	"	"	1,600	"	"	1,520	"	"	79.9	92.8
◎	◎	B16-119-2		◎	◎	S16-119-2		68,500	1	両扉	1,100	900	160	1,020	820	128	135	48.3	55.7
③	③	B16-124-2		③	③	S16-124-2		50,500	1	両扉	1,200	400	160	1,120	320	128	135	27.9	31.2
◎	◎	B16-125-2		③	③	S16-125-2		54,000	1	"	"	500	"	"	420	"	"	32.7	37.0
◎	◎	B16-1610-2		◎	◎	S16-1610-2		104,000	1	両扉	1,600	1,000	160	1,520	920	128	135	78.8	91.7

★両扉の合せ部の有効フカサは上記有効フカサより23mm引いた寸法となります。

フカサ 180mm

◎	◎	B18-355		◎	◎	S18-355		21,500	1	片扉	350	500	180	270	420	148	161	12.0	13.1
◎	◎	B18-46		◎	◎	S18-46		27,500	1	片扉	400	600	180	320	520	148	161	15.2	16.8
◎	◎	B18-57		◎	◎	S18-57		34,000	1	片扉	500	700	180	420	620	148	161	20.4	22.8
◎	◎	B18-69		◎	◎	S18-69		43,500	1	片扉	600	900	180	520	820	148	161	28.9	32.8
◎	◎	B18-611		◎	◎	S18-611		52,500	1	"	"	1,100	"	"	1,020	"	155	34.5	39.3

フカサ 200mm

◎	◎	B20-33		◎	◎	S20-33		14,500	1	片扉	300	300	200	220	220	168	181	7.7	8.3
◎	◎	B20-34		◎	◎	S20-34		19,500	1	"	"	400	"	"	320	"	"	9.5	10.2
◎	◎	B20-35		◎	◎	S20-35		21,500	1	"	"	500	"	"	420	"	"	11.2	12.1
◎	◎	B20-36		◎	◎	S20-36		25,500	1	"	"	600	"	"	520	"	"	13.0	14.1
◎	◎	B20-43		◎	◎	S20-43		19,500	1	片扉	400	300	200	320	220	168	181	9.5	10.2
◎	◎	B20-44		◎	◎	S20-44		22,500	1	"	"	400	"	"	320	"	"	11.6	12.6
◎	◎	B20-45		◎	◎	S20-45		25,500	1	"	"	500	"	"	420	"	"	13.7	15.0
◎	◎	B20-46		◎	◎	S20-46		27,500	1	"	"	600	"	"	520	"	"	15.8	17.3
◎	◎	B20-47		◎	◎	S20-47		33,000	1	"	"	700	"	"	620	"	"	17.8	19.7
◎	◎	B20-48		◎	◎	S20-48		36,000	1	"	"	800	"	"	720	"	"	19.9	22.1
◎	◎	B20-410		◎	◎	S20-410		42,500	1	"	"	1,000	"	"	920	"	175	24.2	27.0
◎	◎	B20-412		◎	◎	S20-412		46,500	1	"	"	1,200	"	"	1,120	"	"	28.4	31.7
◎	◎	B20-457		◎	◎	S20-457		35,000	1	片扉	450	700	200	370	620	168	181	19.4	21.6
◎	◎	B20-53		◎	◎	S20-53		21,500	1	片扉	500	300	200	420	220	168	181	11.3	12.2
◎	◎	B20-54		◎	◎	S20-54		25,500	1	"	"	400	"	"	320	"	"	13.7	15.0
◎	◎	B20-55		◎	◎	S20-55		27,500	1	"	"	500	"	"	420	"	"	16.1	17.8
◎	◎	B20-56		◎	◎	S20-56		31,000	1	"	"	600	"	"	520	"	"	18.6	20.6
◎	◎	B20-57		◎	◎	S20-57		35,000	1	"	"	700	"	"	620	"	"	21.0	23.4
◎	◎	B20-58		◎	◎	S20-58		39,000	1	"	"	800	"	"	720	"	"	23.4	26.2
◎	◎	B20-59		◎	◎	S20-59		42,000	1	"	"	900	"	"	820	"	"	25.8	29.0

◎代理店様在庫品 ◎物流センター在庫品 ①③⑤⑦標準品(納期別) (受)受注品

上記品名記号はライトベージュ塗装です。
クリーム塗装にてご注文の際は品名記号の末尾にCを付けてご用命ください。
価格は同価格です。【例】B16-812-1→B16-812-1Cとなります。

本文の価格には消費税は含まれていません。

キャビネット

盤用

防塵・防水形

小型F(A用)

自立形

熱対策用

情報通信用

特定用途別

計器盤用

ステンレス

キャビネット