


## Ordering Information

### Sensors (Dimensions → page 9)


#### Standard-distance type

##### DC 3-wire, Pre-wired Models (Standard Cable Length: 2 m)

Appearance	Sensing distance	Output	Model	
			Operation mode NO	Operation mode NC
	M12 2 mm	PNP	E2V-X2B1 2M	E2V-X2B2 2M
		NPN	E2V-X2C1 2M	E2V-X2C2 2M
	M18 5 mm	PNP	E2V-X5B1 2M	E2V-X5B2 2M
		NPN	E2V-X5C1 2M	E2V-X5C2 2M
	M30 10 mm	PNP	E2V-X10B1 2M	E2V-X10B2 2M
		NPN	E2V-X10C1 2M	E2V-X10C2 2M


#### Long-distance type

##### DC 3-wire, Pre-wired Models (Standard Cable Length: 2 m)

Appearance	Sensing distance	Output	Model	
			Operation mode NO	Operation mode NC
	M12 4 mm	PNP	E2V-X4B1 2M	E2V-X4B2 2M
		NPN	E2V-X4C1 2M	E2V-X4C2 2M
	M18 8 mm	PNP	E2V-X8B1 2M	E2V-X8B2 2M
		NPN	E2V-X8C1 2M	E2V-X8C2 2M
	M30 15 mm	PNP	E2V-X15B1 2M	E2V-X15B2 2M
		NPN	E2V-X15C1 2M	E2V-X15C2 2M


#### Long-distance type

##### DC 3-wire, Connector Models

Appearance	Sensing distance	Output	Model	
			Operation mode NO	Operation mode NC
	M12 4 mm	PNP	E2V-X4B1-M1	E2V-X4B2-M1
		NPN	E2V-X4C1-M1	E2V-X4C2-M1
	M18 8 mm	PNP	E2V-X8B1-M1	E2V-X8B2-M1
		NPN	E2V-X8C1-M1	E2V-X8C2-M1
	M30 15 mm	PNP	E2V-X15B1-M1	E2V-X15B2-M1
		NPN	E2V-X15C1-M1	E2V-X15C2-M1

#### Long-distance type

##### DC 3-wire, Smartclick Pre-wired Connector (M12) Models

Appearance	Sensing distance	Output	Model
			Operation mode NO
	M12 4 mm	PNP	E2V-X4B1-M1TJ 0.3M
		NPN	E2V-X4C1-M1TJ 0.3M
	M18 8 mm	PNP	E2V-X8B1-M1TJ 0.3M
		NPN	E2V-X8C1-M1TJ 0.3M
	M30 15 mm	PNP	E2V-X15B1-M1TJ 0.3M
		NPN	E2V-X15C1-M1TJ 0.3M