

呼び圧力 10K

SCS13(SUS304)

検査圧力(漏れ)0.6MPa(空圧)

SCS14(SUS316)

単位:mm

| 品名 | 六角ブッシュ | | 6RN 径違いニップル | | RS 径違いソケット | | RS 径違いソケット | | |
|---------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| 形 | | | | | | | | | |
| 状 | | | | | | | | | |
| 呼び径(D) | H ₃ | S ₂ | L ₂ | S ₃ | L ₃ | D ₂ | L ₁ | D ₃ | D ₁ |
| 1/4 × 1/8 | 17 | 14 | 28 | 16 | 25 | 19 | — | — | — |
| 3/8 × 1/8 | 18 | 17 | 29 | 19 | 26 | 22 | — | — | — |
| 3/8 × 1/4 | 18 | 17 | 33 | 19 | 26 | 22 | — | — | — |
| 1/2 × 1/8 | 24 | 24 | — | — | — | — | 34 | 28 | 16.5 |
| 1/2 × 1/4 | 24 | 24 | 36 | 24 | — | — | 34 | 28 | 20 |
| 1/2 × 3/8 | 24 | 24 | 37 | 24 | — | — | 34 | 28 | 23.5 |
| 3/4 × 1/8 | 26 | 29 | — | — | — | — | — | — | — |
| 3/4 × 1/4 | 26 | 29 | — | — | — | — | 36 | 34 | 20 |
| 3/4 × 3/8 | 26 | 29 | 39 | 29 | — | — | 36 | 34 | 23.5 |
| 3/4 × 1/2 | 26 | 29 | 42 | 29 | — | — | 36 | 34 | 28 |
| 1 × 1/4 | 29 | 36 | — | — | — | — | — | — | — |
| 1 × 3/8 | 29 | 36 | — | — | — | — | 43 | 41 | 23.5 |
| 1 × 1/2 | 29 | 36 | 45 | 36 | — | — | 43 | 41 | 28 |
| 1 × 3/4 | 29 | 36 | 47 | 36 | — | — | 43 | 41 | 34 |
| 1 1/2 × 3/8 | 32 | 46 | — | — | — | — | — | — | — |
| 1 1/4 × 1/2 | 32 | 46 | — | — | — | — | 51 | 51 | 28 |
| 1 1/4 × 3/4 | 32 | 46 | 52 | 46 | — | — | 51 | 51 | 34 |
| 1 1/4 × 1 | 32 | 46 | 54 | 46 | — | — | 51 | 51 | 41 |
| 1 1/2 × 1/2 | 34 | 54 | — | — | — | — | — | — | — |
| 1 1/2 × 3/4 | 34 | 54 | — | — | — | — | 55 | 57.5 | 34 |
| 1 1/2 × 1 | 34 | 54 | 57 | 54 | — | — | 55 | 57.5 | 41 |
| 1 1/2 × 1 1/4 | 34 | 54 | 59 | 54 | — | — | 55 | 57.5 | 51 |
| 2 × 1/2 | 40 | 63 | — | — | — | — | — | — | — |
| 2 × 3/4 | 40 | 63 | — | — | — | — | — | — | — |
| 2 × 1 | 40 | 63 | — | — | — | — | 60 | 70 | 41 |
| 2 × 1 1/4 | 40 | 63 | 63 | 63 | — | — | 60 | 70 | 51 |
| 2 × 1 1/2 | 40 | 63 | 64 | 63 | — | — | 60 | 70 | 57.5 |
| 2 1/2 × 1 | 43 | 80 | — | — | — | — | — | — | — |
| 2 1/2 × 1 1/4 | 43 | 80 | — | — | — | — | — | — | — |
| 2 1/2 × 1 1/2 | 43 | 80 | — | — | — | — | 70 | 88.5 | 57.5 |
| 2 1/2 × 2 | 43 | 80 | — | — | — | — | 70 | 88.5 | 70 |
| 3 × 1 | 47 | 95 | — | — | — | — | — | — | — |
| 3 × 1 1/4 | 47 | 95 | — | — | — | — | — | — | — |
| 3 × 1 1/2 | 47 | 95 | — | — | — | — | — | — | — |
| 3 × 2 | 47 | 95 | — | — | — | — | 75 | 102 | 70 |
| 3 × 2 1/2 | 47 | 95 | — | — | — | — | 75 | 102 | 88.5 |
| 4 × 1 1/2 | 52.5 | 120 | — | — | — | — | — | — | — |
| 4 × 2 | 52.5 | 120 | — | — | — | — | — | — | — |
| 4 × 2 1/2 | 52.5 | 120 | — | — | — | — | — | — | — |
| 4 × 3 | 52.5 | 120 | — | — | — | — | — | — | — |

1. □内は引出品です。

2. S₂, S₃は六角部の二面幅です。