


限界プレーンゲージ(PG)

Plain limit gauges



H7
(JIS B 7420)

メートル 通止 Metric GO NOT GO

呼び Size	通止 セット GO NOT GO	
	精度 Class	ツールNo. EDP No. 標準価格 (Yen)
1	H7	9343001 ¥23,400
2	H7	9343002 ¥21,600
3	H7	9343003 ¥19,000
4	H7	9343004 ¥11,020
5	H7	9343005 ¥10,260
6	H7	9343006 ¥9,660
7	H7	9343007 ¥9,660
8	H7	9343008 ¥9,660
9	H7	9343009 ¥10,260
10	H7	9343010 ¥11,020
11	H7	9343011 ¥11,180
12	H7	9343012 ¥11,180
13	H7	9343013 ¥11,180
14	H7	9343014 ¥11,180
15	H7	9343015 ¥11,180
16	H7	9343016 ¥13,240
17	H7	9343017 ¥13,240
18	H7	9343018 ¥13,240
19	H7	9343019 ¥13,240
20	H7	9343020 ¥13,240
21	H7	9343021 ¥15,020
22	H7	9343022 ¥15,020
23	H7	9343023 ¥15,020
24	H7	9343024 ¥15,020
25	H7	9343025 ¥15,020
26	H7	9343026 ¥17,240

呼び Size	通止 セット GO NOT GO	
	精度 Class	ツールNo. EDP No. 標準価格 (Yen)
27	H7	9343027 ¥17,240
28	H7	9343028 ¥17,240
29	H7	9343029 ¥17,240
30	H7	9343030 ¥17,240
31	H7	9343031 ¥20,800
32	H7	9343032 ¥20,800
33	H7	9343033 ¥20,800
34	H7	9343034 ¥20,800
35	H7	9343035 ¥20,800
36	H7	9343036 ¥24,600
37	H7	9343037 ¥24,600
38	H7	9343038 ¥24,600
39	H7	9343039 ¥24,600
40	H7	9343040 ¥24,600
41	H7	9343041 ¥28,800
42	H7	9343042 ¥28,800
43	H7	9343043 ¥28,800
44	H7	9343044 ¥28,800
45	H7	9343045 ¥28,800
46	H7	9343046 ¥32,800
47	H7	9343047 ¥32,800
48	H7	9343048 ¥32,800
49	H7	9343049 ¥32,800
50	H7	9343050 ¥32,800
55	H7	9343051 ¥35,200
60	H7	9343052 ¥37,600

JIS B 7420に準拠しており、JIS B 7421(工作用)相当となります。
Conforms to JIS B 7420, equivalent to JIS B 7421 (working gauge).

在庫区分は全てD(標準在庫品)となります。
Stock are categorized in section D (Standard stock item).