


**表361 : PBIシリーズ寸法表**

単位 : mm

型番	主要寸法							ボール径 インチ(mm) B	$\alpha^\circ$	動定格荷重 C (kN)	質量 (kg)
	d	d <sub>1</sub>	D	W	T	r	H				
<b>PBI5</b>	5	7.7	16	6	8	0.5	1.5	$\frac{1}{8}$ (11.112)	7	2.9	0.010
<b>PBI6</b>	6	9	18	6.7	9	0.5	1.5	$\frac{1}{8}$ (12.7)	11	3.7	0.012
<b>PBI8</b>	8	10.4	22	9	12	0.5	1.5	$\frac{3}{8}$ (15.875)	14	6.5	0.024
<b>PBI10</b>	10	12.9	26	11	14	0.5	1.5	$\frac{3}{8}$ (19.05)	12	9.7	0.040
<b>PBI12</b>	12	15.4	30	12	16	1	2	$\frac{1}{2}$ (22.225)	13	12.2	0.058
<b>PBI14</b>	14	16.9	34	14	19	1	2	1(25.4)	14	16.5	0.086
<b>PBI16</b>	16	19.4	38	15	21	1	2	1 $\frac{1}{8}$ (28.575)	15	20.0	0.116
<b>PBI18</b>	18	21.9	42	17	23	1.5	2.5	1 $\frac{1}{4}$ (31.75)	14	25.1	0.157
<b>PBI20</b>	20	24.4	46	18	25	1.5	2.5	1 $\frac{3}{8}$ (34.925)	14	29.3	0.200
<b>PBI22</b>	22	25.8	50	20	28	1.5	2.5	1 $\frac{1}{2}$ (38.1)	15	35.8	0.262
<b>PBI25</b>	25	29.6	56	22	31	1.5	3	1 $\frac{1}{4}$ (42.862)	15	43.9	0.362
<b>PBI30</b>	30	34.8	66	26	37	2	3	2(50.8)	15	62.2	0.608