

MC703HL 板

幅 mm×長さ mm	600×1200 質量 (kg/ 枚)
厚さ mm	
5	4.0
7	5.6
10	8.0
12	9.6
15	12.0
20	16.0
25	20.0
30	24.0
35	28.0
40	32.0
45	36.0
50	40.0

寸法公差表 (単位: mm)

MC703HL 板

厚さ	公差
5 ~ 20	0 ~ +1.5
25 ~ 45	0 ~ +2.0
50	0 ~ +3.5
幅	公差
600	0 ~ +15.0
長さ	公差
1200	0 ~ +20.0

MC703HL 丸棒

長さ mm	500 質量 (kg/ 本)
外径 mm	
20	0.2
25	0.3
30	0.4
35	0.5
40	0.7
45	0.9
50	1.1

寸法公差表 (単位: mm)

MC703HL 丸棒

外径	公差
20 ~ 35	+0.1 ~ +1.0
40 ~ 50	+0.1 ~ +3.0
長さ	公差
500	+1.0 ~ +15.0

MC703HL パイプ

長さ mm	350 質量 (kg/ 本)	300 質量 (kg/ 本)	500 質量 (kg/ 本)
外径 mm×内径 mm			
50x 25	---	---	0.8
55x 25	---	---	1.1
60x 25	---	---	1.3
65x 25	---	---	1.6
70x 25	---	---	1.9
75x 30	---	---	2.1
80x 30	---	---	2.4
90x 30	---	---	3.1
100x 30	---	---	4.0
110x 35	---	---	4.7
120x 35	---	---	5.7
130x 35	---	---	6.8
140x 40	---	---	7.8
150x 40	---	5.5	---
160x 40	---	6.3	---
175x100	6.3	---	---
175x125	4.6	---	---
180x 40	---	8.1	---
200x 40	---	10.0	---
200x150	5.3	---	---
225x 50	---	12.6	---
225x175	6.1	---	---
250x 50	---	15.7	---
250x200	6.9	---	---
275x 50	---	19.1	---
275x225	7.6	---	---
300x 50	---	22.9	---
300x250	8.4	---	---
350x 50	---	31.4	---
350x300	9.9	---	---
400x350	11.4	---	---

寸法公差表 (単位: mm)

MC703HL パイプ

外径	公差
50 ~ 140	+0.1 ~ +4.0
150 ~ 400	+0.1 ~ +5.0
内径	公差
25 ~ 350	-6.0 ~ -1.0
長さ	公差
300, 350, 500	+1.0 ~ +15.0

*質量については計算値であり、実質量と異なる場合があります。

*黒色 (太字) 数値: 在庫品 青色 (斜体) 数値: 受注生産品