

För icke direkt toleranssatta mått gäller toleransklass
General tolerances if not otherwise stated

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
No sharp edges unless otherwise specified.


LASERMÄRKNING/LASER MARKING:

TEXTFONT: GEN-ISO


Datumkod / Date code "YYYYYY"

Serienummer / Serial number "XXXXXXX"

Rev	Change order	Change: A = Added W = Was D = Deleted C = Changed	Date	Sign
1	1046196000	D 4100-1298A ÄU1046348000 D609.541 W Pat. pend.	100330	SE
2	1052849000	200N W 150N	110825	SE
3	1058686000	4101-7841 W 4101-5828	120521	SE



Övriga generella toleranser enligt ritning 4100-4644.
Additional general tolerances in accordance with drawing 4100-4644.



4101-2610
4101-7841 \triangle_3
4101-6507 U - placering position A
4101-6301
TILLTRYCK PÅ KORT (4101-6301) ENLIGT OMT DOKUMENT NR.:1044540000
PRINTING ON CARD (4101-6301) ACCORDING TO OMT DOCUMENT NO.:1044540000

FÖRSPÄNNING / PRELOAD: 200 ± 20 N

Tolkmått / Gauge dimensions (mm)		
URTAG NEST	Gåtolk GO	Stopptolk NO GO
HEX 3.25	∅3.20	∅3.30
HEX 4.52	∅4.47	∅4.57
HEX 1.69	∅1.66	∅1.72

Packas enligt förpackningsritning 4101-2741
Packed according to drawing 4101-2741

Material		Behandling/Treatment		Status	
Konstr/Design NIJO	Ritad/Drawn MANO	Datum/Date 2012-05-21	Skala/Scale 1:1	Kontr/Checked IP	Godk/Approved NE
pressmaster®			Benämning/Denomination KRIMPTÅNG KCC 0908S		Vikt/Weight,gram 43003690
ISO 9001 REG NR FM13647			CRIMPING TOOL		Art grp 012 REV 003

Den här ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.
This drawing is the property of Pressmaster AB. Protected in accordance with prevailing law.