



給水栓エルボ



●AL

呼び	L	I	B	BD	R
1/2	27	14	6	30	Rc1/2
3/4	32	16	6	36	Rc3/4
1	38	18	7	44	Rc1


給水栓チーழ



●AT

呼び	L	I	B	BD	R
1/2	27	14	6	30	Rc1/2
3/4	32	16	6	36	Rc3/4
1	38	18	7	44	Rc1


給水栓ソケット



●AS

呼び	L	I	B	BD	R
1/2	35	14	6	30	Rc1/2
3/4	40	16	6	36	Rc3/4
1	45	18	7	44	Rc1


B型めすおすソケット(青銅製)



●BX

呼び	L	I	d1	d2	W	R
1/2	45	15	29	10	1.5	R1/2
3/4	53	17	36	15	1.5	R3/4
1	60	19	44	21	2.0	R1
1 1/4	65	22	52	28	2.0	R1 1/4
1 1/2	69	22	59	33	2.0	R1 1/2
2	76	26	73	44	2.0	R2


B C ニップル(青銅製)



●BNI

呼び		L1	L2	二面幅 B
A	B			
15	1/2	42	16	26
20	3/4	47	18	32
25	1	52	20	38
32	1 1/4	56	22	46
40	1 1/2	60	23	54
50	2	66	25	63


給水栓径違いエルボ



●ARL

呼び	L1	L2	I	B1	B2	BD1	BD2	R
3/4 x 1/2	29	30	14	6	6	36	30	Rc1/2
1 x 1/2	32	33	14	7	6	44	30	Rc3/4
1 x 3/4	34	35	16	7	6	44	36	Rc1


給水栓径違いチーழ



●ART

呼び	L1	L2	I	B1	B2	BD1	BD2	R
3/4 x 1/2	29	30	14	6	6	36	30	Rc1/2
1 x 1/2	32	33	14	7	6	44	30	Rc1/2
1 x 3/4	34	35	16	7	6	44	36	Rc3/4

給水栓径違いソケット



●ARS

呼び	L	I	B1	B2	BD1	BD2	R
3/4 x 1/2	38	14	6	6	36	30	Rc1/2
1 x 1/2	42	14	7	6	44	30	Rc1/2
1 x 3/4	42	16	7	6	44	36	Rc3/4