

Accessories for climate control

Filter technology

Spare filter mats

Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100°C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.

For roof-mounted fan

To fit Model No.	Material	W x H x D mm	Filter class to DIN EN 779	Packs of	Model No.
3138..../3139..../3140....	Chemical fibre	264 x 95 x 17	G3	12 pc(s).	3174.100

For EMC fan-and-filter units

To fit Model No.	Material	W x H x D mm	Filter class to DIN EN 779	Packs of	Model No.
3237.6..	Copper-nickel-chrome coated chemical fibres	92 x 92 x 10	G2	5 pc(s).	3237.066
3238.6..	Copper-nickel-chrome coated chemical fibres	125 x 125 x 12	G2	5 pc(s).	3238.066
3239.6..	Copper-nickel-chrome coated chemical fibres	178 x 178 x 17	G3	5 pc(s).	3239.066
3240.6../3241.6..	Copper-nickel-chrome coated chemical fibres	226 x 226 x 17	G3	5 pc(s).	3240.066
3243.6../3244.6../3245.6..	Copper-nickel-chrome coated chemical fibres	294 x 294 x 17	G3	5 pc(s).	3243.066

For fan-and-filter units

To fit Model No.	Material	W x H x D mm	Filter class to DIN EN 779	Packs of	Model No.
3237....	Chemical fibres	89 x 89 x 10	G2	5 pc(s).	3321.700
3237....	Chemical fibres	89 x 89 x 10	G2	50 pc(s).	3321.705
3238....	Chemical fibres	120 x 120 x 12	G2	5 pc(s).	3322.700
3238....	Chemical fibres	120 x 120 x 12	G2	50 pc(s).	3322.705
3239....	Chemical fibres	173 x 173 x 17	G3	5 pc(s).	3171.100
3239....	Chemical fibres	173 x 173 x 17	G3	50 pc(s).	3171.105
3240..../3241....	Chemical fibres	221 x 221 x 17	G3	5 pc(s).	3172.100
3240..../3241....	Chemical fibres	221 x 221 x 17	G3	50 pc(s).	3172.105
3243..../3244..../3245....	Chemical fibres	289 x 289 x 17	G3	5 pc(s).	3173.100
3243..../3244..../3245....	Chemical fibres	289 x 289 x 17	G3	50 pc(s).	3173.105

For Thermoelectric coolers

To fit Model No.	Material	W x H x D mm	Filter class to DIN EN 779	Packs of	Model No.
3201.200/3201.300	Chemical fibre	90 x 106 x 8	G2	5 pc(s).	3201.050

