

ZH330-TiN

ZH330-100-TiN (ロング100型)

ZH330-150-TiN (ロング150型)



外径 φD	刃長 ℓ	胴径 φd	全長 L	公差		シリーズ名 CODE No.	標準価格 TiN
				先端径 φD mm	胴径 φd mm		
0.4	0.6	4	35	+0.1 0	0 -0.012	ZH330-TiN	12,100
	0.6	4	100	+0.1 0	0 -0.012	ZH330-100-TiN	15,600
	0.6	4	150	+0.1 0	0 -0.012	ZH330-150-TiN	17,500
0.5	0.7	4	35	+0.1 0	0 -0.012	ZH330-TiN	12,100
	0.7	4	100	+0.1 0	0 -0.012	ZH330-100-TiN	15,600
	0.7	4	150	+0.1 0	0 -0.012	ZH330-150-TiN	17,500
0.6	0.8	4	35	+0.1 0	0 -0.012	ZH330-TiN	12,100
	0.8	4	100	+0.1 0	0 -0.012	ZH330-100-TiN	15,200
	0.8	4	150	+0.1 0	0 -0.012	ZH330-150-TiN	17,500
0.8	1.0	4	35	+0.1 0	0 -0.012	ZH330-TiN	12,100
	1.0	4	100	+0.1 0	0 -0.012	ZH330-100-TiN	14,800
	1.0	4	150	+0.1 0	0 -0.012	ZH330-150-TiN	17,500
1.0	1.2	4	35	+0.1 0	0 -0.012	ZH330-TiN	12,100
	1.2	4	100	+0.1 0	0 -0.012	ZH330-100-TiN	14,800
	1.2	4	150	+0.1 0	0 -0.012	ZH330-150-TiN	17,500
1.5	2.0	5	40	+0.1 0	0 -0.012	ZH330-TiN	13,000
	2.0	5	100	+0.1 0	0 -0.012	ZH330-100-TiN	17,000
	2.0	5	150	+0.1 0	0 -0.012	ZH330-150-TiN	20,100
2.0	2.5	6	40	+0.1 0	0 -0.015	ZH330-TiN	14,800
	2.5	6	100	+0.1 0	0 -0.015	ZH330-100-TiN	18,500
	2.5	6	150	+0.1 0	0 -0.015	ZH330-150-TiN	22,100
2.5	3.2	8	50	+0.1 0	0 -0.015	ZH330-TiN	17,500
	3.2	8	100	+0.1 0	0 -0.015	ZH330-100-TiN	22,800
	3.2	8	150	+0.1 0	0 -0.015	ZH330-150-TiN	28,400
3.0	3.6	8	50	+0.12 0	0 -0.015	ZH330-TiN	17,900
	3.6	8	100	+0.12 0	0 -0.015	ZH330-100-TiN	22,800
	3.6	8	150	+0.12 0	0 -0.015	ZH330-150-TiN	28,400
4.0	4.8	10	65	+0.12 0	0 -0.015	ZH330-TiN	23,300
	4.8	10	100	+0.12 0	0 -0.015	ZH330-100-TiN	32,400
	4.8	10	150	+0.12 0	0 -0.015	ZH330-150-TiN	37,500
5.0	6.5	12	70	+0.12 0	0 -0.018	ZH330-TiN	30,900
	6.5	12	100	+0.12 0	0 -0.018	ZH330-100-TiN	35,400
	6.5	12	150	+0.12 0	0 -0.018	ZH330-150-TiN	42,500
6.0	8.0	16	70	+0.15 0	0 -0.018	ZH330-TiN	44,600
	8.0	16	100	+0.15 0	0 -0.018	ZH330-100-TiN	53,000
	8.0	16	150	+0.15 0	0 -0.018	ZH330-150-TiN	67,700