



■ Insert (Coated Carbide / Cermet / Carbide / SUMIBORON / SUMIDIA)

- 7° Relief G-Class
- Coated SUMIBORON One-use Type/Multi-corner

2NC-CCGW		Stock					Dimensions (mm)				
		BNC2010	BNC2020	BNC100	BNC160	BNC200	BNC300	BNC500	Inscribed Circle	Thickness	Nose Radius
Cat. No.											
2NC-CCGW 060202		●	●					6.35	2.38	0.2	
060204		●	●							0.4	
060208										0.8	
060202LS						●				0.2	
060204LS						●				0.4	
2NC-CCGW 09T302		●	●	●	●	●	●	9.525	3.97	0.2	
09T304		●	●	●	●	●	●			0.4	
09T308		●	●	●	●	●	●			0.8	
09T304WG		●	●	●	●	●	●			0.4	
09T308WG		●	●	●	●	●	●			0.8	
09T304WH		●	●	●	●	●	●			0.4	
09T308WH		●	●	●	●	●	●			0.8	
09T302LS						●				0.2	
09T304LS						●				0.4	
09T308LS				●	●	●				0.8	
09T304HS						●				0.4	
09T308HS						●				0.8	

* WG/WH: Wiper Insert, LS: Small Edge Treatment Type, HS: Strong Edge Type

- Coated SUMIBORON Break Master

2NC-CCGT		Stock				Dimensions (mm)		
		BNC2010	BNC2020	BNC160	BNC200	Inscribed Circle	Thickness	Nose Radius
Cat. No.								
2NC-CCGT 060204N-FV		●	●	●	●	6.35	2.38	0.4
2NC-CCGT 09T304N-FV		●	●	●	●			0.4
09T308N-FV		●	●	●	●	9.525	3.97	0.8
09T304N-LV		●	●	●	●			0.4
09T308N-LV		●	●	●	●			0.8

- 7° Relief M-Class
- SUMIDIA (NF Type)

NF-CCMT		Stock				Dimensions (mm)		
		DA1000	DA2200			Inscribed Circle	Thickness	Nose Radius
Cat. No.								
NF-CCMT 060201		●	▲			6.35	2.38	0.1
060202		●	▲					0.2
060204		●	▲					0.4
NF-CCMT 09T301		●	▲			9.525	3.97	0.1
09T302		●	▲					0.2
09T304		●	▲					0.4
09T308		●	▲					0.8

- SUMIDIA (Break Master)

NF-CCMT		Stock				Dimensions (mm)		
		DA1000				Inscribed Circle	Thickness	Nose Radius
Cat. No.								
NF-CCMT 060202N-LD		●				6.35	2.38	0.2
060204N-LD		●						0.4
060202N-GD		●						0.2
060204N-GD		●						0.4
NF-CCMT 09T302N-LD		●				9.525	3.97	0.2
09T304N-LD		●						0.4
09T308N-LD		●						0.8
09T302N-GD		●						0.2
09T304N-GD		●						0.4
09T308N-GD		●						0.8

NU-CCMT		Stock				Dimensions (mm)		
		DA150				Inscribed Circle	Thickness	Nose Radius
Cat. No.								
NU-CCMT 060202R-DM		●				6.35	2.38	0.2
060202L-DM		●						0.2
060204R-DM		●						0.4
060204L-DM		●						0.4
NU-CCMT 09T302R-DM		●				9.525	3.97	0.2
09T302L-DM		●						0.2
09T304R-DM		●						0.4
09T304L-DM		●						0.4

- SUMIDIA

CCMT		Stock				Dimensions (mm)		
		DA150	DA2200			Inscribed Circle	Thickness	Nose Radius
Cat. No.								
CCMT 060201		●	▲			6.35	2.38	0.1
060202		●	▲					0.2
060204		●	▲					0.4
CCMT 09T301		●	▲			9.525	3.97	0.1
09T302		●	▲					0.2
09T304		●	▲					0.4