

# Spanners

## Spanners

Spanner (Hexagonal)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	L	L				
	LH015	●	1.5	45	14	—	—	—	—
	LH020	●	2	50	16	—	—	—	—
	LH025	●	2.5	56	18	—	—	—	—
	LH030	●	3	63	20	—	—	—	—
	LH035	●	3.5	68	22	—	—	—	—
	LH040	●	4	70	25	—	—	—	—
	LH050	●	5	80	28	—	—	—	—
	LH060	●	6	90	32	—	—	—	—
Spanner (Hexagonal)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	L	L				
	LH020NT	●	2	50	16	—	—	—	—
	LH025NT	●	2.5	56	6.0	—	—	—	—
Spanner (Torx)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	d	L	L			
	LT08-06	●	T8	2.3	45.0	6.0	—	—	—
	LT15	●	T15	T15	54	17.9	—	—	—
	LT20	●	T20	3.9	57.2	19.1	—	—	—
	LT25	●	T25	4.4	60.3	20.2	—	—	—
	LT27	●	T27	4.96	63.5	21.5	—	—	—
Spanner (Torx Plus)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	d	L	L			
	LT25NT	●	25IP	4	65	10	—	—	—
Tee Hex Spanner (Hexagonal)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	b1	C				
	TH030	●	3	48	28	—	—	—	—
	TH040	●	4	48	37	—	—	—	—
	TH050	●	5	48	45	—	—	—	—
Tee Hex Spanner (Hexagonal)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	b1	C				
	TH015	●	1.5	35	30	—	—	—	—
	TH020	●	2	35	39	—	—	—	—
	TH025	●	2.5	35	39	—	—	—	—
Hex Spanner (Hexagonal)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	C	b1	b2			
	TSW040	●	4	60	20	40	—	—	—
Hex Spanner (Screwdriver Type)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	C	b1				
	HD040	●	4	75	111	—	—	—	—

## Spanners

Tee Spanner (Torx)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	d	C	b1			
	TTX15W	●	T15	4.0	97	28	—	—	—
	TTX20	●	T20	3.9	58	47	—	—	—
	TT25	●	T25	4.4	27	48	—	—	—
	TT27	●	T27	5.0	41	48	—	—	—
Special Torx Spanner	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	C	b1	b2			
	TRX06	●	T6	35.5	15	15	—	—	—
	TRX08	●	T8	38.5	19	19	—	—	—
	TRX10	●	T10	42.1	22	22	—	—	—
	TRX15	●	T15	46	22	27	—	—	—
	TRX20	●	T20	49	22	30	—	—	—
Special Torx Plus Spanner	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			d	C	b1	b2			
	RT06	●	2	35	15	15	—	—	—
Tee Spanner (Torx Plus)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	d	C	b1			
	TTR15 IP	●	15IP	4.0	80	25.5	—	—	—
Special Torx Plus Spanner (Screwdriver Type)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	C	b1				
	TRDR08 IP	●	8IP	60	104	—	—	—	—
	TRDR10 IP	●	10IP	80	111	—	—	—	—
	TRDR15 IP	●	15IP	80	111	—	—	—	—
	TRDR20 IP	●	20IP	100	118	—	—	—	—
	TRDR25 IP	●	25IP	100	118	—	—	—	—
Special Torx Spanner (Screwdriver Type)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			B	d	C	b1			
	TRD07	●	T7	2.0	45	70	—	—	—
	TRD08	●	T8	2.3	55	70	—	—	—
	TRD15	●	T15	3.9	70	100	—	—	—
	TRD20	●	T20	4.6	100	90	—	—	—
	TRD25	●	T25	5.3	80	110	—	—	—
Key Spanner	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			L	a	C				
	KY25	●	45	2.5	—	10	—	—	—
	KY40	●	60	4	—	13	—	—	—
	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)
			d	C	b1	b2			
	RFT	●	1.7	35	15	15	—	—	—