

ユニファイねじ呼寸と山数(ピッチ)

Unified limit thread gauge of nominal diameter and pitch

呼 び		外 径 (インチ)	山数 (山/インチ)			山数 (山/インチ) ……系列ねじ								呼 び
			UNC	UNF	UNEF	4UN	6UN	8UN	12UN	16UN	20UN	28UN	32UN	
No.0	No.1 No.2 No.3 No.4 No.5 No.6 No.8 No.10 No.12	0.06	—	80	—	—	—	—	—	—	—	—	—	No.0
		0.073	64	72	—	—	—	—	—	—	—	—	—	No.1
No.2		0.086	56	64	—	—	—	—	—	—	—	—	—	No.2
		0.099	48	56	—	—	—	—	—	—	—	—	—	No.3
No.4		0.112	40	48	—	—	—	—	—	—	—	—	—	No.4
No.5		0.125	40	44	—	—	—	—	—	—	—	—	—	No.5
No.6		0.138	32	40	—	—	—	—	—	—	—	—	—	No.6
No.8		0.164	32	36	—	—	—	—	—	—	—	—	—	No.8
No.10		0.19	24	32	—	—	—	—	—	—	—	—	—	No.10
		0.216	24	28	32	—	—	—	—	—	—	—	—	No.12
1/4	11/16 13/16 15/16	0.25	20	28	32	—	—	—	—	—	—	—	—	1/4
5/16		0.3125	18	24	32	—	—	—	—	—	20	28	—	5/16
3/8		0.375	16	24	32	—	—	—	—	—	20	28	—	7/8
7/16		0.4375	14	20	28	—	—	—	—	16	—	—	32	7/16
1/2		0.5	13	20	28	—	—	—	—	16	—	—	32	1/2
9/16		0.5625	12	18	24	—	—	—	—	16	20	28	32	9/16
5/8		0.625	11	18	24	—	—	—	12	16	20	28	32	5/8
		0.6875	—	—	24	—	—	—	12	16	20	28	32	11/16
3/4		0.75	10	16	20	—	—	—	12	16	—	28	32	3/4
		0.8125	—	—	20	—	—	—	12	16	—	28	32	13/16
	0.875	9	14	20	—	—	—	12	16	—	28	32	7/8	
	0.9375	—	—	20	—	—	—	12	16	—	28	32	15/16	
1	1 1/16 1 3/16 1 5/16 1 7/16 1 9/16 1 11/16 1 13/16 1 15/16	1	8	12	20	—	—	—	—	16	—	28	32	1
		1.0625	—	—	18	—	—	8	12	16	20	28	—	1 1/16
1 1/8		1.125	7	12	18	—	—	8	—	16	20	28	—	1 1/8
		1.1875	—	—	18	—	—	8	12	16	20	28	—	1 3/16
1 1/4		1.25	7	12	18	—	—	8	—	16	20	28	—	1 1/4
		1.3125	—	—	18	—	—	8	12	16	20	28	—	1 5/16
1 3/8		1.375	6	12	18	—	—	8	—	16	20	28	—	1 3/8
		1.4375	—	—	18	—	6	8	12	16	20	28	—	1 7/16
1 1/2		1.5	6	12	18	—	—	8	—	16	20	28	—	1 1/2
		1.5625	—	—	18	—	6	8	12	16	20	—	—	1 9/16
1 5/8	1.625	—	—	18	—	6	8	12	16	20	—	—	1 5/8	
	1.6875	—	—	18	—	6	8	12	16	20	—	—	1 11/16	
1 3/4	1.75	5	—	—	—	6	8	12	16	20	—	—	1 3/4	
	1.8125	—	—	—	—	6	8	12	16	20	—	—	1 13/16	
1 7/8	1.875	—	—	—	—	6	8	12	16	20	—	—	1 7/8	
	1.9375	—	—	—	—	6	8	12	16	20	—	—	1 15/16	
2	2 1/8 2 3/8 2 5/8 2 7/8	2	4 1/2	—	—	—	6	8	12	16	20	—	—	2
		2.125	—	—	—	—	6	8	12	16	20	—	—	2 1/8
2 1/4		2.25	4 1/2	—	—	—	6	8	12	16	20	—	—	2 1/4
		2.375	—	—	—	—	6	8	12	16	20	—	—	2 3/8
2 1/2		2.5	4	—	—	—	6	8	12	16	20	—	—	2 1/2
		2.625	—	—	—	4	6	8	12	16	20	—	—	2 5/8
2 3/4	2.75	4	—	—	—	6	8	12	16	20	—	—	2 3/4	
	2.875	—	—	—	4	6	8	12	16	20	—	—	2 7/8	
3	3 1/8 3 3/8 3 5/8 3 7/8	3	4	—	—	—	6	8	12	16	20	—	—	3
		3.125	—	—	—	4	6	8	12	16	—	—	—	3 1/8
3 1/4		3.25	4	—	—	—	6	8	12	16	—	—	—	3 1/4
		3.375	—	—	—	4	6	8	12	16	—	—	—	3 3/8
3 1/2		3.5	4	—	—	—	6	8	12	16	—	—	—	3 1/2
		3.625	—	—	—	4	6	8	12	16	—	—	—	3 5/8
3 3/4	3.75	4	—	—	—	6	8	12	16	—	—	—	3 3/4	
	3.875	—	—	—	4	6	8	12	16	—	—	—	3 7/8	
4	4 1/8 4 1/4 4 3/8 4 5/8 4 7/8	4	4	—	—	—	—	—	—	—	—	—	—	4
		4.125	—	—	—	4	6	8	12	16	—	—	—	4 1/8
4 1/4		4.25	—	—	—	4	6	8	12	16	—	—	—	4 1/4
		4.375	—	—	—	4	6	8	12	16	—	—	—	4 3/8
4 1/2		4.5	—	—	—	4	6	8	12	16	—	—	—	4 1/2
		4.625	—	—	—	4	6	8	12	16	—	—	—	4 5/8
4 3/4	4.75	—	—	—	4	6	8	12	16	—	—	—	4 3/4	
	4.875	—	—	—	4	6	8	12	16	—	—	—	4 7/8	
5	5 1/8 5 3/8 5 5/8 5 7/8	5	—	—	—	4	6	8	12	16	—	—	—	5
		5.125	—	—	—	4	6	8	12	16	—	—	—	5 1/8
5 1/4		5.25	—	—	—	4	6	8	12	16	—	—	—	5 1/4
		5.375	—	—	—	4	6	8	12	16	—	—	—	5 3/8
5 1/2		5.5	—	—	—	4	6	8	12	16	—	—	—	5 1/2
		5.625	—	—	—	4	6	8	12	16	—	—	—	5 5/8
5 3/4	5.75	—	—	—	4	6	8	12	16	—	—	—	5 3/4	
	5.875	—	—	—	4	6	8	12	16	—	—	—	5 7/8	
6		6	—	—	—	4	6	8	12	16	—	—	6	

【例】1/4 - 28UNFとなります。(注) 上記のいずれにも該当しないユニファイねじは、UNS (特殊ねじ) となります。