

# Heavy Duty Stopper Cylinder

# 25A-RSH Series

∅20, ∅32

RoHS



## How to Order

**25A-RSH** **32** **-** **20** **D** **L** **-** **M9BW**

Series compatible with secondary batteries

• **Bore size**

20	20 mm
32	32 mm

• **Port thread type**

Nil	M*1
	Rc
TN	NPT
TF	G

\*1 The tube I.D. of 20 is only available to port size M screws.

• **Cylinder stroke**

15	15 mm (RSH20)
20	20 mm (RSH32)

• **Number of auto switches**

Nil	2
S	1

• **Auto switch**

Nil Without auto switch (Built-in magnet)

\* For applicable auto switches, refer to page 258.

• **Roller material**

L	Resin
M	Carbon steel

• **Action**

D	Double acting type
B	Double acting spring type
T	Single acting/Spring extended

\* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the **Web Catalog**.