

重荷重  
중하중  
HEAVY LOAD



하중 荷重 ±10%  
직각도 直角度 2° 以下  
자유장 自由長 50m/m 以下 ±0.5m/m  
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load

SH 8×10	8	4	10	8.80	2.4	21	2.2	19	1.9	17
15			15	5.86	3.6		3.2		2.9	
20			20	4.40	4.8		4.3		3.8	
25			25	3.52	6.0		5.4		4.8	
30			30	2.93	7.2		6.5		5.8	
35			35	2.51	8.4		7.6		6.7	
40			40	2.20	9.6		8.6		7.7	
45			45	1.95	10.8		9.7		8.6	
50			50	1.76	12.0		10.8		9.6	
55			55	1.60	13.2		11.9		10.6	
60			60	1.47	14.4		13.0		11.5	
65			65	1.35	15.6		14.0		12.5	
70			70	1.26	16.8		15.1		13.4	
75			75	1.17	18.0		16.2		14.4	
80	80	1.10	19.2	17.3	15.4					
90	90	0.98	21.6	19.4	17.3					
SH 10×10	10	5	10	12.27	2.4	30	2.2	27	1.9	24
15			15	8.18	3.6		3.3		2.9	
20			20	6.25	4.8		4.3		3.8	
25			25	5.00	6.0		5.4		4.8	
30			30	4.16	7.2		6.5		5.8	
35			35	3.57	8.4		7.6		6.7	
40			40	3.15	9.6		8.6		7.7	
45			45	2.77	10.8		9.7		8.6	
50			50	2.50	12.0		10.8		9.6	
55			55	2.27	13.2		11.9		10.6	
60			60	2.08	14.4		13.0		11.5	
65			65	1.92	15.6		14.0		12.5	
70			70	1.79	16.8		15.1		13.4	
75			75	1.67	18.0		16.2		14.4	
80	80	1.56	19.2	17.3	15.4					
90	90	1.39	21.6	19.4	17.3					
100	100	1.25	24.0	21.6	19.2					