



## NYLON AUTOESTINGUENTE V0: UL 94 ESENTE DA ALOGENI, MASSIMA SICUREZZA AL FUOCO

- EN** NYLON SELF EXTINGUISHING, V0: UL 94 HALOGEN-FREE, FIRE-PROOF MAXIMUM SECURITY
- FR** NYLON AUTO-EXTINGUIBLE V0: UL 94 SANS HALOGÈNES HAUTE SÉCURITÉ AU FEU
- ES** NYLON AUTOEXTINGUIBLE V0: UL 94 LIBRE DE HALÓGENOS MÁXIMA SEGURIDAD CONTRA EL FUEGO
- DE** NYLON SELBSTLÖSCHEND V0: UL 94, HALOGENFREI, MAXIMALE FEUERSICHERHEIT
- PT** NYLON AUTOEXTINGUÍVEL V0: UL 94, ISENTAS DE HALOGÉNEOS, SEGURANÇA MÁXIMA AO FOGO

 mm				 mm	 kg daN	
100x2,5	5.000	100	<input type="checkbox"/>	2 ÷ 24	9	<b>SEL.EC2.202R</b>
200x3,5	5.000	100	<input type="checkbox"/>	3 ÷ 55	16	<b>SEL.EC2.211R</b>
280x4,5	5.000	100	<input type="checkbox"/>	5 ÷ 76	23	<b>SEL.EC2.425R</b>
360x7,5	1.500	100	<input type="checkbox"/>	5 ÷ 101	55	<b>SEL.EC2.434R</b>
540x7,5	1.000	100	<input type="checkbox"/>	20 ÷ 160	55	<b>SEL.EC2.437R</b>