


FOR CONSTRUCTION WORK

NO.75L Long Taper Point Bit



S=Size O/A=Overall Length T/L=Twist Length SD=Shank-Dia
Unit mm


Size	O/A Length	Twist Length	Shank-Dia
4mm	165	100	6.35
5mm	180	115	6.35
6mm	180	115	6.35



NO.75HT H.S.S.Taper Point Bit (Titanium Coating)



Perfect for Hard Wood. High Durability.



S=Size O/A=Overall Length T/L=Twist Length SD=Shank-Dia
Unit mm

Size	Contents of Set	O/A Length	Twist Length	Shank-Dia
A set	3 · 4 · 5mm			6.35
B set	4 · 5 · 6mm			6.35
3mm		110	45	6.35
4mm		125	60	6.35
5mm		135	70	6.35
6mm		135	70	6.35

