


LS形



呼び形番	スライダ寸法								
	最大 ストローク l_s	高さ M ± 0.25	幅 W ± 0.25	長さ L	T	L_1	B	F	$S \times l$
	LS 827	13	8	14.2	29.6	7.6	26	5.5	16
LS 852	25	8	14.2	54.6	7.6	51	5.5	41	M2×2.7
LS 877	50	8	14.2	79.6	7.6	76	5.5	66	M2×2.7
LS 1027	13	10	19	29.6	9.2	26	8.5	16	M3×3.2
LS 1052	25	10	19	54.6	9.2	51	8.5	41	M3×3.2
LS 1077	50	10	19	79.6	9.2	76	8.5	66	M3×3.2