

No. 23 『タテ・ヨコ・兼用刃』

品番	外径	刃厚	内径	刃数	刃型	定価	NET	JANコード
MK-80	80	1.8	20	24	中心交互刃	¥5,500		4949022 000413
MK-100	100	1.8	20	30	中心交互刃	¥4,600		4949022 000420
MK-110	110	1.8	20	30	中心交互刃	¥4,600		4949022 000437
MK140-127	140	1.4	12.7	40	交互刃	¥4,600		4949022 004237
MK140-20	140	1.4	20	40	交互刃	¥4,600		4949022 000451
MK203-40	203	2.2	25.4	40	交互刃	¥8,000		4949022 000567
MK203-50	203	2.2	25.4	50	交互刃	¥10,000		4949022 000574
MK203-60	203	2.2	25.4	60	交互刃	¥11,300		4949022 000581
MK210-50	210	2.2	25.4	50	交互刃	¥10,300		4949022 000611
MK216-40	216	2.2	25.4	40	交互刃	¥9,200		4949022 000642
MK216-50	216	2.2	25.4	50	交互刃	¥10,300		4949022 000659
MK216-60	216	2.2	25.4	60	交互刃	¥12,300		4949022 000666
MK218-50	218	2.2	25.4	50	交互刃	¥10,300		4949022 000697
MK235-40	235	2.0	25.4	40	交互刃	¥9,200		4949022 000703
MK235-50	235	2.0	25.4	50	交互刃	¥10,300		4949022 000710
MK235-60	235	2.0	25.4	60	交互刃	¥12,300		4949022 000727
MK255-40	255	2.0	25.4	40	交互刃	¥9,500		4949022 000734
MK255-50	255	2.0	25.4	50	交互刃	¥10,500		4949022 000741
MK255-60	255	2.0	25.4	60	交互刃	¥12,500		4949022 000758
MK260-50	260	2.2	25.4	50	交互刃	¥11,200		4949022 000840
MK272-50	272	2.2	25.4	50	交互刃	¥11,200		4949022 000857
MK290-50	290	2.2	25.4	50	交互刃	¥11,800		4949022 000888
MK305-40	305	2.2	25.4	40	交互刃	¥10,000		4949022 000918
MK305-50	305	2.2	25.4	50	交互刃	¥11,800		4949022 000925
MK305-60	305	2.2	25.4	60	交互刃	¥13,500		4949022 000932
MK320-50	320	2.6	25.4	50	交互刃	¥12,200		4949022 000970
MK335-50	335	2.6	25.4	50	交互刃	¥12,200		4949022 000987
MK335-60	335	2.6	25.4	60	交互刃	¥14,300		4949022 000994
MK355-50	355	2.6	25.4	50	交互刃	¥12,200		4949022 001021
MK355-60	355	2.6	25.4	60	交互刃	¥14,300		4949022 001038
MK362-50	362	2.6	25.4	50	交互刃	¥12,200		4949022 001076
MK380-50	380	2.6	25.4	50	交互刃	¥12,600		4949022 001090
Mk380-60	380	2.6	25.4	60	交互刃	¥14,800		4949022 001106
Mk405-50	405	3.0	25.4	50	交互刃	¥17,200		4949022 001168
MK405-60	405	3.0	25.4	60	交互刃	¥20,900		4949022 001175
MK415-50	415	3.0	25.4	50	交互刃	¥20,000		4949022 001212
MK415-60	415	3.0	25.4	60	交互刃	¥23,300		4949022 001229
MK455-60	455	3.2	25.4	60	交互刃	¥35,200		4949022 001250
MK455-80	455	3.2	25.4	80	交互刃	¥39,000		4949022 001267
MK510-60	510	3.2	25.4	60	交互刃	¥44,700		4949022 001298
MK510-80	510	3.2	25.4	80	交互刃	¥50,200		4949022 001304
MK560-60	560	3.2	25.4	60	交互刃	¥61,200		4949022 001335
MK560-80	560	3.4	25.4	80	交互刃	¥64,700		4949022 001342
MK610-60	610	3.4	25.4	60	交互刃	¥69,900		4949022 001373
MK610-80	610	3.6	25.4	80	交互刃	¥78,400		4949022 001380

