

Please request / order by indicating the combination part number as below.

FCW 5 - 20 - 15handle type
(N or K)color code
(GS, BS, BX or BB)

Part no. / Dimensions

Part no.	H	W	D	Weight(kg)	Handle pcs	Hinge pcs
FCW5-15-20□□□	50.4	150	200	0.69	1	2
FCW5-15-25□□□	50.4	150	250	0.80	1	2
FCW5-20-15□□□	50.4	200	150	0.69	1	2
FCW5-20-20□□□	50.4	200	200	0.83	1	2
FCW5-20-25□□□	50.4	200	250	0.97	1	2
FCW5-20-30□□□	50.4	200	300	1.11	1	2
FCW5-25-25□□□	50.4	250	250	1.14	1	2
FCW5-25-30□□□	50.4	250	300	1.30	1	2
FCW5-25-40□□□	50.4	250	400	1.63	1	2
FCW5-30-20□□□	50.4	300	200	1.11	1	2
FCW5-30-30□□□	50.4	300	300	1.50	1	2
FCW5-30-40□□□	50.4	300	400	1.87	1	2
FCW5-30-50□□□	50.4	300	500	2.28	2	3
FCW5-35-25□□□	50.4	350	250	1.47	1	2
FCW5-40-30□□□	50.4	400	300	1.88	1	2
FCW5-40-40□□□	50.4	400	400	2.37	1	2
FCW5-40-50□□□	50.4	400	500	2.82	2	3
FCW5-40-60□□□	50.4	400	600	3.28	2	3
FCW6-15-20□□□	62.9	150	200	0.72	1	2
FCW6-15-25□□□	62.9	150	250	0.84	1	2
FCW6-20-15□□□	62.9	200	150	0.72	1	2
FCW6-20-20□□□	62.9	200	200	0.86	1	2
FCW6-20-25□□□	62.9	200	250	1.01	1	2
FCW6-20-30□□□	62.9	200	300	1.16	1	2
FCW6-25-25□□□	62.9	250	250	1.18	1	2
FCW6-25-30□□□	62.9	250	300	1.35	1	2
FCW6-25-40□□□	62.9	250	400	1.69	1	2
FCW6-30-20□□□	62.9	300	200	1.16	1	2
FCW6-30-30□□□	62.9	300	300	1.55	1	2
FCW6-30-40□□□	62.9	300	400	1.93	1	2
FCW6-30-50□□□	62.9	300	500	2.35	2	3
FCW6-35-25□□□	62.9	350	250	1.46	1	2
FCW6-40-30□□□	62.9	400	300	1.94	1	2
FCW6-40-40□□□	62.9	400	400	2.44	1	2
FCW6-40-50□□□	62.9	400	500	2.94	2	3
FCW6-40-60□□□	62.9	400	600	3.36	2	3
FCW8-15-20□□□	75.4	150	200	0.76	1	2
FCW8-15-25□□□	75.4	150	250	0.88	1	2
FCW8-20-15□□□	75.4	200	150	0.76	1	2
FCW8-20-20□□□	75.4	200	200	0.91	1	2
FCW8-20-25□□□	75.4	200	250	1.06	1	2
FCW8-20-30□□□	75.4	200	300	1.21	1	2
FCW8-25-25□□□	75.4	250	250	1.24	1	2
FCW8-25-30□□□	75.4	250	300	1.41	1	2
FCW8-25-40□□□	75.4	250	400	1.76	1	2
FCW8-30-20□□□	75.4	300	200	1.21	1	2
FCW8-30-30□□□	75.4	300	300	1.62	1	2
FCW8-30-40□□□	75.4	300	400	2.02	1	2
FCW8-30-50□□□	75.4	300	500	2.44	2	3
FCW8-35-25□□□	75.4	350	250	1.59	1	2
FCW8-40-30□□□	75.4	400	300	2.02	1	2
FCW8-40-40□□□	75.4	400	400	2.53	1	2
FCW8-40-50□□□	75.4	400	500	3.05	2	3
FCW8-40-60□□□	75.4	400	600	3.47	2	3

Part no.	H	W	D	Weight(kg)	Handle pcs	Hinge pcs
FCW10-15-20□□□	100.4	150	200	0.83	1	2
FCW10-15-25□□□	100.4	150	250	0.97	1	2
FCW10-20-15□□□	100.4	200	150	0.83	1	2
FCW10-20-20□□□	100.4	200	200	1.00	1	2
FCW10-20-25□□□	100.4	200	250	1.17	1	2
FCW10-20-30□□□	100.4	200	300	1.33	1	2
FCW10-25-25□□□	100.4	250	250	1.36	1	2
FCW10-25-30□□□	100.4	250	300	1.55	1	2
FCW10-25-40□□□	100.4	250	400	1.93	1	2
FCW10-30-20□□□	100.4	300	200	1.34	1	2
FCW10-30-30□□□	100.4	300	300	1.77	1	2
FCW10-30-40□□□	100.4	300	400	2.20	1	2
FCW10-30-50□□□	100.4	300	500	2.64	2	3
FCW10-35-25□□□	100.4	350	250	1.74	1	2
FCW10-40-30□□□	100.4	400	300	2.21	1	2
FCW10-40-40□□□	100.4	400	400	2.74	1	2
FCW10-40-50□□□	100.4	400	500	3.27	2	3
FCW10-40-60□□□	100.4	400	600	3.71	2	3
FCW13-15-20□□□	125.4	150	200	0.89	1	2
FCW13-15-25□□□	125.4	150	250	1.04	1	2
FCW13-20-15□□□	125.4	200	150	0.89	1	2
FCW13-20-20□□□	125.4	200	200	1.06	1	2
FCW13-20-25□□□	125.4	200	250	1.32	1	2
FCW13-20-30□□□	125.4	200	300	1.41	1	2
FCW13-25-25□□□	125.4	250	250	1.44	1	2
FCW13-25-30□□□	125.4	250	300	1.63	1	2
FCW13-25-40□□□	125.4	250	400	2.02	1	2
FCW13-30-20□□□	125.4	300	200	1.41	1	2
FCW13-30-30□□□	125.4	300	300	1.94	1	2
FCW13-30-40□□□	125.4	300	400	2.30	1	2
FCW13-30-50□□□	125.4	300	500	2.74	2	3
FCW13-35-25□□□	125.4	350	250	1.83	1	2
FCW13-40-30□□□	125.4	400	300	2.30	1	2
FCW13-40-40□□□	125.4	400	400	2.86	1	2
FCW13-40-50□□□	125.4	400	500	3.39	2	3
FCW13-40-60□□□	125.4	400	600	3.84	2	3
FCW15-15-20□□□	150.4	150	200	0.96	1	2
FCW15-15-25□□□	150.4	150	250	1.07	1	2
FCW15-20-15□□□	150.4	200	150	0.91	1	2
FCW15-20-20□□□	150.4	200	200	1.18	1	2
FCW15-20-25□□□	150.4	200	250	1.37	1	2
FCW15-20-30□□□	150.4	200	300	1.57	1	2
FCW15-25-25□□□	150.4	250	250	1.59	1	2
FCW15-25-30□□□	150.4	250	300	1.80	1	2
FCW15-25-40□□□	150.4	250	400	2.23	1	2
FCW15-30-20□□□	150.4	300	200	1.57	1	2
FCW15-30-30□□□	150.4	300	300	2.05	1	2
FCW15-30-40□□□	150.4	300	400	2.53	1	2
FCW15-30-50□□□	150.4	300	500	2.99	2	3
FCW15-35-25□□□	150.4	350	250	2.02	1	2
FCW15-40-30□□□	150.4	400	300	2.53	1	2
FCW15-40-40□□□	150.4	400	400	3.12	1	2
FCW15-40-50□□□	150.4	400	500	3.68	2	3
FCW15-40-60□□□	150.4	400	600	4.14	2	3