

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items

TSL Hole Saw



- Features**
- Because of long blade length, it adapts to drilling in a wide range of fields.
 - **Using our own cobalt bi-metal blade.**
 - With spring for discharge.
 - With unequal pitch blade shape, stable cutting and light drilling on wood have been realized
- Materials**
- Blade Part: Cobalt Bi-Metal (SKH59)
 - Center Drills: High Speed Steel (SKH51)
- Origin**
- Japan

Item No.	Blade Thickness (mm) (cutting width including clipper)
TSL-12 to 14	1.96
TSL-15 to 65	2.07
TSL-66 to 150	2.27

*Clipper refers saw's shape spreading inside/outside.

Warning
• For cutting above 3.2mm, please use the spring removed.

Iron Plate 3.2mm
Cast Metal 3.2mm
AL Plate 3.2mm
Vinyl Chloride 12mm
Plywood Until throat depth
Gypsum Board Until throat depth
Stainless Plate 1mm

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Throat Height (mm)	Shank Diameter (mm)	Blade Thickness (mm)	SPQ (piece)	Weight (g)
328-7297	TSL-12	¥1,701	¥2,100	12	27	6	0.92	5	50
328-7301	TSL-13	¥1,701	¥2,100	13	27	6	0.92	5	50
328-7319	TSL-14	¥1,701	¥2,100	14	27	6	0.92	5	50
231-7559	TSL-15	¥1,701	¥2,100	15	27	10	1.07	5	50
231-7567	TSL-16	¥1,701	¥2,100	16	27	10	1.07	5	60
231-7575	TSL-17	¥1,701	¥2,100	17	27	10	1.07	5	60
231-7583	TSL-18	¥1,701	¥2,100	18	27	10	1.07	5	60
231-7591	TSL-19	¥1,701	¥2,100	19	27	10	1.07	5	70
231-7605	TSL-20	¥1,888	¥2,330	20	27	10	1.07	5	90
231-7613	TSL-21	¥1,888	¥2,330	21	27	10	1.07	5	90
231-7621	TSL-22	¥1,888	¥2,330	22	27	10	1.07	5	100
231-7630	TSL-23	¥1,888	¥2,330	23	27	10	1.07	5	100
231-7648	TSL-24	¥1,888	¥2,330	24	27	10	1.07	5	100
231-7656	TSL-25	¥2,252	¥2,780	25	27	10	1.07	5	120
231-7664	TSL-26	¥2,252	¥2,780	26	27	10	1.07	5	120
231-7672	TSL-27	¥2,252	¥2,780	27	27	10	1.07	5	120
231-7681	TSL-28	¥2,252	¥2,780	28	27	10	1.07	5	130
231-7699	TSL-29	¥2,252	¥2,780	29	27	10	1.07	5	130
231-7702	TSL-30	¥2,520	¥3,110	30	27	10	1.07	5	130
231-7711	TSL-31	¥2,520	¥3,110	31	27	10	1.07	5	140
231-7729	TSL-32	¥2,520	¥3,110	32	27	10	1.07	5	140
231-7737	TSL-33	¥2,520	¥3,110	33	27	10	1.07	5	150
231-7745	TSL-34	¥2,520	¥3,110	34	27	10	1.07	5	150
231-7753	TSL-35	¥2,989	¥3,690	35	34	10	1.07	5	180
231-7761	TSL-36	¥2,989	¥3,690	36	34	10	1.07	3	190
231-7770	TSL-37	¥2,989	¥3,690	37	34	10	1.07	3	200
231-7788	TSL-38	¥2,989	¥3,690	38	34	10	1.07	3	200
231-7796	TSL-39	¥2,989	¥3,690	39	34	10	1.07	3	200
231-7800	TSL-40	¥3,467	¥4,280	40	34	10	1.07	3	210
231-7818	TSL-41	¥3,467	¥4,280	41	34	10	1.07	3	220
231-7826	TSL-42	¥3,467	¥4,280	42	34	10	1.07	3	220
231-7834	TSL-43	¥3,467	¥4,280	43	34	10	1.07	3	230
231-7842	TSL-44	¥3,467	¥4,280	44	34	10	1.07	3	230
231-7851	TSL-45	¥3,929	¥4,850	45	34	10	1.07	3	240
231-7869	TSL-46	¥3,929	¥4,850	46	34	10	1.07	3	250
231-7877	TSL-47	¥3,929	¥4,850	47	34	10	1.07	3	280
231-7885	TSL-48	¥3,929	¥4,850	48	34	10	1.07	3	280
231-7893	TSL-49	¥3,929	¥4,850	49	34	10	1.07	3	290
231-7907	TSL-50	¥4,464	¥5,510	50	34	10	1.07	3	290
231-7915	TSL-51	¥4,464	¥5,510	51	34	10	1.07	3	300
231-7923	TSL-52	¥4,464	¥5,510	52	34	10	1.07	3	310

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Throat Height (mm)	Shank Diameter (mm)	Blade Thickness (mm)	SPQ (piece)	Weight (g)
231-7931	TSL-53	¥ 4,464	¥ 5,510	53	34	10	1.07	3	310
231-7940	TSL-54	¥ 4,464	¥ 5,510	54	34	10	1.07	3	320
231-7958	TSL-55	¥ 4,933	¥ 6,090	55	34	10	1.07	3	320
231-7966	TSL-56	¥ 4,933	¥ 6,090	56	34	10	1.07	1	340
231-7974	TSL-57	¥ 4,933	¥ 6,090	57	34	10	1.07	1	360
231-7982	TSL-58	¥ 4,933	¥ 6,090	58	34	10	1.07	1	360
231-7991	TSL-59	¥ 4,933	¥ 6,090	59	34	10	1.07	1	370
231-8008	TSL-60	¥ 5,508	¥ 6,800	60	34	10	1.07	1	370
231-8016	TSL-61	¥ 5,508	¥ 6,800	61	34	12	1.07	1	360
231-8024	TSL-62	¥ 5,508	¥ 6,800	62	34	12	1.07	1	360
231-8032	TSL-63	¥ 5,508	¥ 6,800	63	34	12	1.07	1	360
231-8041	TSL-64	¥ 5,508	¥ 6,800	64	34	12	1.07	1	360
231-8059	TSL-65	¥ 5,954	¥ 7,350	65	34	12	1.07	1	370
231-8067	TSL-66	¥ 5,954	¥ 7,350	66	38	12	1.27	1	390
231-8075	TSL-67	¥ 5,954	¥ 7,350	67	38	12	1.27	1	400
231-8083	TSL-68	¥ 5,954	¥ 7,350	68	38	12	1.27	1	400
231-8091	TSL-69	¥ 5,954	¥ 7,350	69	38	12	1.27	1	410
231-8105	TSL-70	¥ 6,424	¥ 7,930	70	38	12	1.27	1	410
231-8113	TSL-71	¥ 6,424	¥ 7,930	71	38	12	1.27	1	450
231-8121	TSL-72	¥ 6,424	¥ 7,930	72	38	12	1.27	1	450
231-8130	TSL-73	¥ 6,424	¥ 7,930	73	38	12	1.27	1	470
231-8148	TSL-74	¥ 6,424	¥ 7,930	74	38	12	1.27	1	470
231-8156	TSL-75	¥ 6,877	¥ 8,490	75	38	12	1.27	1	470
231-8164	TSL-76	¥ 6,877	¥ 8,490	76	38	12	1.27	1	470
231-8172	TSL-77	¥ 6,877	¥ 8,490	77	38	12	1.27	1	480
231-8181	TSL-78	¥ 6,877	¥ 8,490	78	38	12	1.27	1	480
231-8199	TSL-79	¥ 6,877	¥ 8,490	79	38	12	1.27	1	500
231-8202	TSL-80	¥ 7,639	¥ 9,430	80	38	12	1.27	1	500
231-8211	TSL-85	¥ 8,352	¥10,310	85	38	12	1.27	1	520
231-8229	TSL-90	¥ 8,724	¥10,770	90	38	12	1.27	1	550
231-8237	TSL-95	¥ 9,283	¥11,460	95	38	12	1.27	1	590
231-8245	TSL-100	¥ 9,283	¥11,460	100	38	12	1.27	1	630
231-8253	TSL-105	¥21,368	¥26,380	105	38	13	1.27	1	930
231-8261	TSL-110	¥22,324	¥27,560	110	38	13	1.27	1	960
231-8270	TSL-115	¥23,272	¥28,730	115	38	13	1.27	1	1010
231-8288	TSL-120	¥24,089	¥29,740	120	38	13	1.27	1	1080
231-8296	TSL-125	¥25,045	¥30,920	125	38	13	1.27	1	1120
231-8300	TSL-130	¥25,864	¥31,930	130	38	13	1.27	1	1170
231-8318	TSL-140	¥27,630	¥34,110	140	38	13	1.27	1	1310
231-8326	TSL-150	¥31,437	¥38,810	150	38	13	1.27	1	1420



TSL-665 (Center Drill)

Center Drill

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Total Length (mm)	Compatible Model	SPQ (piece)	Weight (g)
277-5298	TSL-660	¥527	¥ 650	6	60	TSL-15 to 34	10	13
277-5280	TSL-665	¥705	¥ 870	6	65	TSL-12 to 14	10	12
277-5301	TSL-675	¥567	¥ 700	6	75	TSL-35 to 46	10	14
277-5310	TSL-885	¥981	¥1,210	8	85	TSL-47 to 150	10	26

Contact us: 0120-509-849 <http://www.orange-book.com/>

Drills

Coated Carbide Drills

Carbide Drills

High Speed Steel Coated Drills

High Speed Steel Drills

Thin Shaft Drills

Spot Cutters

Taper Shank Drills

Hex Shank Ironsmith Drills

Drill Sets

Drill Cases

Step Drills

Cutters for Magnetic Cutting Unit

Hole Saws

Core Drills

Concrete Drills

Drills

Bits, Cutters for Wood

For other cutting tools, see p. 1-805 to 1006