

Prices displayed include 8% tax.

For Air Reel, see p. 3-375 to 384

Fluid Couplings • Tubes

TRUSCO Stock 38,650 Items

Air Hose (with one-touch coupling)



- Features**
- Super soft type and excellent usability.
 - Can connect with common couplings. (except for some)
 - To prevent entanglement, special processing which is slippery on the surface is applied.
- Specs**
- Working Fluid: Air
 - Working temperature: -10 to 60°C
 - Working Pressure: 1.5MPa
- Materials**
- PVC Elastomer
- Origin**
- Japan



TWCH-7-10

Order Unit: 1 Roll

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	SPQ (roll)	Weight (kg)
380-3414	TWCH-7-5	¥ 4,166	¥ 4,500	Orange	10.0 x 7.0	5	10	0.47
380-3422	TWCH-7-10	¥ 5,073	¥ 5,480	Orange	10.0 x 7.0	10	10	0.74
380-3431	TWCH-7-20	¥ 6,906	¥ 7,460	Orange	10.0 x 7.0	20	6	1.28
380-3449	TWCH-7-30	¥ 8,730	¥ 9,430	Orange	10.0 x 7.0	30	5	1.82
380-3457	TWCH-85-5	¥ 4,980	¥ 5,380	Orange	12.5 x 8.5	5	10	0.60
380-3465	TWCH-85-10	¥ 6,341	¥ 6,850	Orange	12.5 x 8.5	10	10	1.10
380-3473	TWCH-85-20	¥ 9,072	¥ 9,800	Orange	12.5 x 8.5	20	6	1.85
380-3481	TWCH-85-30	¥ 11,803	¥ 12,750	Orange	12.5 x 8.5	30	5	2.65

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Air Hose (with swing coupling)



- Features**
- Super soft type and excellent usability.
 - At the time of separation, residual pressure automatically comes off, recoil and unpleasant sounds are also reduced.
 - Can connect with common couplings. (except for some)
 - To prevent entanglement, special processing which is slippery on the surface is applied.
- Specs**
- Working Fluid: Air
 - Working temperature: -10 to 60°C
 - Working Pressure: 1.5MPa
- Materials**
- PVC Elastomer
- Origin**
- Japan



TSRC-7-10

Order Unit: 1 Roll

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	SPQ (roll)	Weight (kg)
309-4049	TSRC-7-10	¥ 6,721	¥ 7,260	Orange	10.0 x 7.0	10	10	0.80
309-4057	TSRC-7-20	¥ 9,368	¥ 10,120	Orange	10.0 x 7.0	20	6	1.40
309-4065	TSRC-7-30	¥ 12,219	¥ 13,200	Orange	10.0 x 7.0	30	5	2.00
309-4073	TSRC-85-10	¥ 8,248	¥ 8,910	Orange	12.5 x 8.5	10	10	1.10
309-4081	TSRC-85-20	¥ 11,812	¥ 12,760	Orange	12.5 x 8.5	20	6	1.85
309-4090	TSRC-85-30	¥ 15,274	¥ 16,500	Orange	12.5 x 8.5	30	5	2.65

Contact us: 0120-509-849 <http://www.orange-book.com/>

Video



TRUSCO Stock 38,650 Items

High Pressure Hose (with one-touch coupling)



- Features**
- To prevent entanglement, special processing which is slippery on the surface is applied.
 - Super soft type and excellent usability.
- Specs**
- Working Fluid: Air
 - Working temperature: -10 to 60°C
 - Working Pressure: 3.0MPa
 - Compatible Air Reel: TAHP-D
- Materials**
- PVC Elastomer
- Origin**
- Japan




THP-5-20

Order Unit: 1 Roll

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Inner Diameter x Outer Diameter (mm)	Total Length (m)	SPQ (roll)	Weight (kg)
275-4851	THP-5-10	¥ 10,461	¥ 11,300	Dark Green	5 x 9	10	10	0.95
275-4860	THP-5-20	¥ 14,534	¥ 15,700	Dark Green	5 x 9	20	6	1.45
275-4878	THP-5-30	¥ 18,699	¥ 20,200	Dark Green	5 x 9	30	5	2.00
275-4886	THP-6-10	¥ 12,034	¥ 13,000	Dark Green	6 x 10	10	10	1.00
275-4894	THP-6-20	¥ 17,589	¥ 19,000	Dark Green	6 x 10	20	6	1.55
275-4908	THP-6-30	¥ 23,143	¥ 25,000	Dark Green	6 x 10	30	5	2.10

Contact us: 0120-509-849 <http://www.orange-book.com/>



Warning

- Uses high pressure type sockets and plugs.

For High Pressure Air Reel, see p. 3-384

⚠ Artificial shock, bending, tension may cause damage!