

# Tipped Saws (for building materials/for aluminum)

The number next to the logo mark indicates items in stock for each brand.

Cutting Supplies

Cutting Wheels

Tip Saws

Diamond Cutters

Metal Saws

Band Saws

Machine Saws

Hand Hacksaws

Saw Blades

Air Saw Blades

Jig Saw Blades



Stock 38,650 Items

## All-Purpose Tipped Saw



- Features**
- 1 blade can be used to cut anything from aluminum materials to iron materials.
  - Black fluorine coating suppresses the adhesion of resins and adhesives.
  - Easy cutting of even materials that have nail inside.
  - It comes with convenient cutting depth markings.
  - Same price setting even with the larger size.

**Use** • For cutting wooden materials, aluminum, iron, etc. and cutting apart large trash.  
**Materials** • Base Metal: Tool Steel • Tip: Carbide  
**Origin** • China



TSM A-165

Order Unit: 1 Sheet

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Cutting Performance (mm)			Outer Diameter x Blade Thickness x Hole Diameter (mm)	Number of Blades	Max Working Rotation Speed (rpm)	SPQ (sheet)	Weight (g)
				Wood	Iron Plate	Angle					
855-0212	TSM A-100	¥1,462	¥1,580	27	1.5	3	100 x 1.4 x 20	36	15200	10	67
855-0213	TSM A-127	¥1,462	¥1,580	46	1.5	3	127 x 1.4 x 20	42	12200	10	112
855-0214	TSM A-147	¥1,462	¥1,580	57	1.5	3	147 x 1.6 x 20	52	10500	10	184
855-0215	TSM A-165	¥1,462	¥1,580	66	1.5	3	165 x 1.6 x 20	52	9200	10	214
855-0216	TSM A-190	¥1,462	¥1,580	68	1.5	3	190 x 1.6 x 20	52	8000	10	287

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

## Tipped Saw "Aluminum Cut"



- Features**
- A tipped saw that uses a high precision base metal and has a flexible tip so it is hard to chip even with unstable work.
  - A tipped saw for professionals that is long life and high work efficiency.

**Use** • Aluminum building materials in general such as aluminium sashes and aluminum siding, non-iron metals (copper, brass, light alloys, etc.)

**Materials** • Base Metal: Tool Steel • Tip: Carbide  
**Origin** • Japan

**Warning**  
 • Cannot be used with disk grinders.



TSA-18058

Order Unit: 1 Sheet

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Cutting Performance (mm)	Aluminum	Outer Diameter x Blade Thickness x Hole Diameter (mm)	Number of Blades	Max Working Rotation Speed (rpm)	SPQ (sheet)	Weight (g)
478-9598	TSA-12542	¥ 3,870	¥ 4,180	3		125 x 1.5 x 20.0	42	9600	10	86
478-9601	TSA-16052	¥ 4,277	¥ 4,620	3		160 x 1.8 x 20.0	52	6000	10	205
478-9610	TSA-18058	¥ 4,582	¥ 4,950	3		180 x 1.8 x 20.0	58	5500	10	262
837-0575	TSA-21680	¥ 12,497	¥ 13,500	3		216 x 2.2 x 25.4	80	5000	10	442
837-0576	TSA-255100	¥ 14,997	¥ 16,200	5		255 x 2.2 x 25.4	100	4000	10	626
837-0577	TSA-305100	¥ 15,737	¥ 17,000	5		305 x 2.4 x 25.4	100	4000	5	1013
837-0578	TSA-355100	¥ 18,977	¥ 20,500	5		355 x 2.4 x 25.4	100	3500	5	1375
837-0579	TSA-405120	¥ 26,383	¥ 28,500	5		405 x 2.6 x 25.4	120	3500	5	1973

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 249 Items

## Tipped Saw "Global Saw" (for aluminum and non-iron metals)



- Features** • Aluminum tip and blade type makes it possible to cut quickly.

**Use** • Aluminum sash for cutting aluminum made material.

**Materials** • Base Metal: Tool Steel • Tip: Carbide  
**Origin** • Japan

Order Unit: 1 Sheet

(Price revision date: Apr, 2015) MOTOYUKI Co.Ltd

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Cutting Performance (mm)	Aluminum	Outer Diameter x Blade Thickness x Hole Diameter (mm)	Number of Blades	Max Working Rotation Speed (rpm)	SPQ (sheet)	Weight (g)
279-1218	GA-110E	¥ 6,326	¥ 8,200	3		110 x 1.6 x 20.0	36	13000	10	100
836-1904	GA-150E	¥ 6,634	¥ 8,600	3		150 x 1.4 x 20.0	52	6000	10	140
279-1226	GA-160E	¥ 7,406	¥ 9,600	3		160 x 2.0 x 20.0	50	6000	10	220
279-1234	GA-180E	¥ 7,869	¥ 10,200	3		180 x 2.0 x 20.0	54	5500	10	250
379-3028	GA-190E	¥ 8,331	¥ 10,800	3		190 x 2.0 x 20.0	60	5500	10	300
379-3036	GA-210-80	¥ 12,729	¥ 16,500	5		210 x 2.2 x 25.4	80	5000	1	500
279-1242	GA-216-80	¥ 12,729	¥ 16,500	5		216 x 2.2 x 25.4	80	5000	1	450
279-1251	GA-216-100	¥ 14,889	¥ 19,300	5		216 x 2.2 x 25.4	100	5000	1	550
379-3061	GA-255-80	¥ 14,040	¥ 18,200	5		255 x 2.4 x 25.4	80	4000	1	650
379-3044	GA-255-100	¥ 16,817	¥ 21,800	5		255 x 2.4 x 25.4	100	4000	1	750
379-3052	GA-255-120	¥ 19,517	¥ 25,300	5		255 x 2.4 x 25.4	120	4000	1	800
379-3079	GA-260-80	¥ 14,040	¥ 18,200	5		260 x 2.4 x 25.4	80	4000	1	900
279-1269	GA-305-100	¥ 17,666	¥ 22,900	5		305 x 2.8 x 25.4	100	4000	1	1600
379-3087	GA-305-120	¥ 19,517	¥ 25,300	5		305 x 2.8 x 25.4	120	4000	1	1800
359-7806	GA-355-100	¥ 22,911	¥ 29,700	5		355 x 2.8 x 25.4	100	3500	1	2040
379-3095	GA-355-120	¥ 24,609	¥ 31,900	5		355 x 2.8 x 25.4	120	3500	1	2100
379-3109	GA-380-100	¥ 24,454	¥ 31,700	5		380 x 2.8 x 25.4	100	3500	1	2200
379-3117	GA-380-120	¥ 25,920	¥ 33,600	5		380 x 2.8 x 25.4	120	3500	1	2200
279-1277	GA-405-120	¥ 30,394	¥ 39,400	5		405 x 3.0 x 25.4	120	3500	1	2900
379-3125	GA-455-120	¥ 37,183	¥ 48,200	5		455 x 3.0 x 25.4	120	3500	1	2800

Contact us: 0120-278-423 <http://www.motoyuki.co.jp/>

Please wear protective equipment to use safely.