

Umbrella Type Brushes with Shaft

The number next to the logo mark indicates items in stock for each brand.

TRUSCO



Stock 38,650 Items

Umbrella Type Brush



Com Drawing



30WKH-6 40WKH-6
Wire brush (half round type)

- Features**
- Capable of polishing the bottom surface and the side surface at the same time.
 - Attached to a rotating tool such as an automation machine or drill press for use.
- Use**
- For rust and dirt removal of various metals, cleaning before and after welding, and polishing of the bottom and inner diameter of cylinders.
 - **Working tool: electric drill, drill press, etc.**
- Materials**
- Shaft: Steel Origin • Japan
- Warning**
- Air tools cannot be used.
 - Please use below The maximum working rotation speed. Please wear protective equipment to use safely.

Wire brush (half round type)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Length x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
402-6837	20WKH-6	¥1,851	¥2,000	0.3	Steel Wire	20 x 15 x 25 x 6	3000	1	40
402-6845	25WKH-6	¥1,851	¥2,000	0.3	Steel Wire	25 x 15 x 25 x 6	3000	1	40
402-6853	30WKH-6	¥2,037	¥2,200	0.3	Steel Wire	30 x 25 x 35 x 6	3000	1	75
402-6861	35WKH-6	¥2,037	¥2,200	0.3	Steel Wire	35 x 25 x 35 x 6	3000	1	80
402-6870	40WKH-6	¥2,499	¥2,700	0.3	Steel Wire	40 x 30 x 35 x 6	3000	1	135

TRUSCO NAKAYAMA CORPORATION

Wire brush (square type)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Length x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
402-6888	20WKK-6	¥1,851	¥2,000	0.3	Steel Wire	20 x 15 x 25 x 6	3000	1	40
402-6896	25WKK-6	¥1,851	¥2,000	0.3	Steel Wire	25 x 15 x 25 x 6	3000	1	40
402-6900	30WKK-6	¥2,037	¥2,200	0.3	Steel Wire	30 x 25 x 35 x 6	3000	1	75
402-6918	35WKK-6	¥2,037	¥2,200	0.3	Steel Wire	35 x 25 x 35 x 6	3000	1	80
402-6926	40WKK-6	¥2,499	¥2,700	0.3	Steel Wire	40 x 30 x 35 x 6	3000	1	135

Stainless steel brush (half round type)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Length x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
402-6934	20SKH-6	¥2,314	¥2,500	0.3	Stainless Steel	20 x 15 x 25 x 6	3000	1	40
402-6942	25SKH-6	¥2,314	¥2,500	0.3	Stainless Steel	25 x 15 x 25 x 6	3000	1	40
402-6951	30SKH-6	¥2,777	¥3,000	0.3	Stainless Steel	30 x 25 x 35 x 6	3000	1	75
402-6969	35SKH-6	¥2,777	¥3,000	0.3	Stainless Steel	35 x 25 x 35 x 6	3000	1	80
402-6977	40SKH-6	¥3,147	¥3,400	0.3	Stainless Steel	40 x 30 x 35 x 6	3000	1	135

Stainless steel brush (square type)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Length x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
402-6985	20SKK-6	¥2,314	¥2,500	0.3	Stainless Steel	20 x 15 x 25 x 6	3000	1	40
402-6993	25SKK-6	¥2,314	¥2,500	0.3	Stainless Steel	25 x 15 x 25 x 6	3000	1	40
402-7001	30SKK-6	¥2,777	¥3,000	0.3	Stainless Steel	30 x 25 x 35 x 6	3000	1	75
402-7019	35SKK-6	¥2,777	¥3,000	0.3	Stainless Steel	35 x 25 x 35 x 6	3000	1	80
402-7027	40SKK-6	¥3,147	¥3,400	0.3	Stainless Steel	40 x 30 x 35 x 6	3000	1	135

Contact us: 0120-509-849 <http://www.orange-book.com/>

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes

TRUSCO



Stock 38,650 Items

Umbrella Type Brush

Com Drawing



83K-2 Hard Steel Wire 83K-3 Brass 83K-4 Stainless Steel 103K-2 Hard Steel Wire 103K-3 Brass 103K-4 Stainless Steel

- Features**
- Easy to mount/replacement with the shaft.
 - Umbrella type brush that is easy to operate due to compact and high-speed rotation, excellent usability.
- Use**
- Since it is an umbrella type, it is optimum for polishing cylindrical inner diameter and bottom part.
 - **Working Tool: Variable speed type electric micro grinder.**
- Materials**
- Shaft: Brass Origin • Japan

- Warning**
- Air tools cannot be used.
 - Please use below The maximum working rotation speed. Please wear protective equipment to use safely.



Example

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Length x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	Comments	SPQ (piece)	Weight (g)
415-2476	83K-2	¥962	¥1,040	0.1	Hard Steel Wire	8 x 8 x 36 x 3	10000	Delamination and grinding of metal products	1	3.3
415-2484	83K-3	¥723	¥780	0.1	Brass	8 x 8 x 36 x 3	10000	Polishing of brass, copper products and alloy products	1	3.3
415-2492	83K-4	¥842	¥910	0.1	Stainless Steel	8 x 8 x 36 x 3	10000	Polishing of stainless steel, aluminum products	1	3.3
415-2506	103K-2	¥962	¥1,040	0.1	Hard Steel Wire	10 x 8 x 36 x 3	10000	Delamination and grinding of metal products	1	3.3
415-2514	103K-3	¥723	¥780	0.1	Brass	10 x 8 x 36 x 3	10000	Polishing of brass, copper products and alloy products	1	3.3
415-2522	103K-4	¥842	¥910	0.1	Stainless Steel	10 x 8 x 36 x 3	10000	Polishing of stainless steel, aluminum products	1	3.3

Contact us: 0120-509-849 <http://www.orange-book.com/>