

Prices displayed include 8% tax.

For Construction Work Supplies, see p. 7-33 to 35

TRUSCO Stock 38,650 Items

## Propane Burner

Repairing OK

Com Drawing



Extra-fine concentrated flame TB-SS1 (SS type)



Spiral concentrated flame TB-S3 (S type)



Rod-like Flame TB-M3 (M type)



User Manual



(nozzle for propane burner)




TB-H3MB (hose for propane burner (with valve))



TB-M100S



TB-M300S



TB-M700S (joint for propane burner)

- Features**
- A burner for brazing which does not require an oxygen cylinder and regulator.
  - With air adjuster on hand
  - Hose: 3m (TB-H3MB)
  - Japan
- Specs**
- Origin**

Item No.	Air adjuster
TB-SS1	Yes
TB-S1	Yes
TB-S2	None
TB-S3	None
TB-M3	None
TB-M5	None
TB-M6	None



You can adjust flame by turning the air conditioner at hand only for TB-SS1・TB-S1.

\*As for the hose, 2m (TB-H2MB) or 5m (TB-H5MB) hose can be set. (The hose is separately delivered. Please contact us for the delivery date.)

### SS Type

Use • Brazing work of copper pipes, stainless steel pipes, and brazing, processing, quenching and tempering of bites.

Order Unit: 1 Set

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Flame Temperature (°C)	Heat Output (kcal/h)	Nozzle Outer Diameter (mm)	Flame dimension (mm) Length x Diameter	SPQ (set)	Weight (kg/set)
231-0414	TB-SS1	¥16,663	¥18,000	800 to 1800	1600	12	115 x 5	6	1.1

### S Type

Use • Brazing of copper pipes, stainless steel pipes, brazing processing of bites, metal quenching, tempering.

Order Unit: 1 Set

(Price revision date: Jan, 2016)

Order Code	Item No.	Price (per set)	MSRP (per set)	Flame Temperature (°C)	Heat Output (kcal/h)	Nozzle Outer Diameter (mm)	Flame dimension (mm) Length x Diameter	SPQ (set)	Weight (kg/set)
231-0422	TB-S1	¥16,663	¥18,000	800 to 1800	7200	17	180 x 25	6	1.1
231-0431	TB-S2	¥17,700	¥19,120	1800	9600	21	230 x 35	6	1.1
231-0449	TB-S3	¥18,329	¥19,800	1800	12000	28	290 x 45	6	1.2

### M Type

Use • Linoleum floor construction. • Cedar burning, wood root burning.

Order Unit: 1 Set

(Price revision date: Jan, 2016)

Order Code	Item No.	Price (per set)	MSRP (per set)	Flame Temperature (°C)	Heat Output (kcal/h)	Nozzle Outer Diameter (mm)	Flame dimension (mm) Length x Diameter	SPQ (set)	Weight (kg/set)
231-0457	TB-M3	¥16,570	¥17,900	1500	4800	25	230 x 25	6	1.2
231-0465	TB-M5	¥17,357	¥18,750	1500	12000	35	350 x 35	6	1.2
231-0473	TB-M6	¥18,393	¥19,870	1500	25000	50	400 x 50	6	1.3

### Nozzle for Propane Burner

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Flame Temperature (°C)	Nozzle Outer Diameter (mm)	Length (mm)	Materials	SPQ (piece)	Weight (g)
818-5112	TB-3H	¥ 3,888	¥ 4,200	1500	25	79	Stainless Steel	1	79
273-5563	TB-5H	¥ 4,166	¥ 4,500	1500	35	92	Stainless Steel	1	140
273-5571	TB-6H	¥ 4,814	¥ 5,200	1500	50	112	Stainless Steel	1	197
273-5580	TB-7H	¥ 5,415	¥ 5,850	1500	60	138	Stainless Steel	1	327
273-5598	TB-8H	¥ 6,480	¥ 7,000	1500	75	160	Iron	1	587
430-9031	TB-10H	¥12,960	¥14,000	1500	100	200	Iron	1	1340
818-5111	TB-SS1H	¥ 7,017	¥ 7,580	1800	12	150	Brass	1	140
818-5108	TB-S1H	¥ 7,017	¥ 7,580	1800	17	165	Brass	1	150
818-5109	TB-S2H	¥ 8,211	¥ 8,870	1800	21	160	Brass	1	150
818-5110	TB-S3H	¥ 8,582	¥ 9,270	1800	28	170	Brass	1	200

### Hose for Propane Burner(with valve)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Hose Length (m)	SPQ (piece)	Weight (kg)
273-5601	TB-H2MB	¥10,090	¥10,900	2	1	0.85
273-5610	TB-H3MB	¥10,646	¥11,500	3	1	1.01
273-5628	TB-H5MB	¥12,219	¥13,200	5	1	1.33
818-5113	TB-H10MB	¥16,449	¥17,770	10	1	2.33

### Joint for Propane Burner

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Joint thickness x length (mm)	Cap nut size (mm)	SPQ (piece)	Weight (g)
430-9065	TB-M100S	¥3,055	¥3,300	12 x 130	M20 x P1	1	120
430-9073	TB-M300S	¥3,888	¥4,200	12 x 310	M20 x P1	1	180
430-9081	TB-M700S	¥4,166	¥4,500	12 x 590	M20 x P1	1	260

Contact us:0120-509-849 <http://www.orange-book.com/>

Welding Machines

Engine Welders

Spot Welders

Plasma Cutting Machines

Welding Tables

Welding Rods

Accessories for Welding Equipment

Welding Scale Removers

Gas Torches

Gas Burners

Gas Cutting Equipments

Gas Regulators

Brazing Filler Metals

Welding Masks

Protective Eyewears for Welding

Protective Tools for Welding

Spatter Sheets

Protective Fences for Welding

Industrial Markers