

The number next to the logo mark indicates items in stock for each brand.

- Desks
- PC Desks
- Meeting Tables
- Cafeteria Tables
- Office Chairs
- Meeting Chairs
- Working Chairs
- Anti-Static Stools
- Benches
- Umbrella Stands
- Reception Room Furnitures
- Hanger Racks
- Partitions
- Book Cabinets
- Counters
- Filing Cabinets
- Catalog Cases
- Map Cases/Letter Cases
- Pamphlet Stands
- File Wagons
- Lockers
- Shoes Boxes
- Safes
- Mailboxes
- Key Boxes
- Window Films
- Interior Blinds
- OA Floors
- System Kitchens



Stock 38,650 Items

Mesh Chair



Require 1 Persons
15 minutes



MC-5A

- Features**
- Office chair having various functions such as adjustment of the rocking strength/weakness and angle and adjustment of the height of the armrest part.
 - Since mesh material is used for the back, it has excellent breathability.
- Specs**
- Adjustable seat function: Gas control type
 - Type with lifting/lowering arms
 - Synchronous rocking function
 - With lifting/lowering lumbar support function
- Materials**
- Back: PP Plastic Molded Part (mesh)
 - Lumbar support: PP resin molded part
 - Seat: Molded Plywood, Urethane Foam, Cloth
 - Elbow part: PP resin molded item, Armrest: PU resin molded item
 - Leg: Reinforced Resin Molded Product, φ50 Urethane Twin-wheel Caster
- Origin**
- China

Mounting example of headrest



Order Unit: 1 Piece

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Coated Cloth	Color	Seat Width x Washer Depth x Seat Height (mm)	Weight (kg)
414-3744	MC-5A	¥36,973	¥39,940	Upholstery	Black	495 x 450 x 430 to 500	17.5

Dedicated headrest

- Specs**
- Lifting/lowering function
 - Angle adjusting function
- Materials**
- PP resin molded item, urethane foam, fabric

(Price revision date: Jan, 2016)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	SPQ (piece)	Weight (kg)
414-3761	MC-5M	¥6,786	¥7,330	Black	1	0.7

Dedicated hanger

- Materials**
- PP Plastic Molded Item

(Price revision date: Jan, 2016)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	SPQ (piece)	Weight (kg)
414-3752	MC-5HG	¥5,526	¥5,970	Black	1	0.1

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Mesh Chair




Require 1 Persons
15 minutes



MC-2-BK (armless/black)

- Features**
- The back part uses mesh material pursuing breath ability, is a comfortable office chair with comfortable feeling.
- Specs**
- Adjustable seat function: Gas control type
 - Back Locking Function
- Materials**
- Back: PP Plastic Molded Part (mesh)
 - Seat: Molded Plywood, Urethane Foam, Cloth
 - Leg: Reinforced Resin Molded Product, φ50 Urethane Twin-wheel Caster
- Origin**
- China



Armless Type

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Coated Cloth	Color	Seat Width x Washer Depth x Seat Height (mm)	Weight (kg)
414-3817	MC-2-B	¥18,422	¥19,900	Upholstery	Blue	470 x 450 x 450 to 540	11.2
414-3825	MC-2-BK	¥18,422	¥19,900	Upholstery	Black	470 x 450 x 450 to 540	11.2
414-3833	MC-2-YG	¥18,422	¥19,900	Upholstery	Yellow Green	470 x 450 x 450 to 540	11.2



Lift Lever

With Arm Type

- Materials**
- Arm Part: PP Resin Molded Item

(Price revision date: Jan, 2016)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Coated Cloth	Color	Seat Width x Washer Depth x Seat Height (mm)	Weight (kg)
414-3779	MC-2A-B	¥22,273	¥24,060	Upholstery	Blue	470 x 450 x 450 to 540	12.7
414-3787	MC-2A-BK	¥22,273	¥24,060	Upholstery	Black	470 x 450 x 450 to 540	12.7
414-3809	MC-2A-YG	¥22,273	¥24,060	Upholstery	Yellow Green	470 x 450 x 450 to 540	12.7

Exclusive Elbow

- Materials**
- PP Plastic Molded Item

(Price revision date: Jan, 2016)

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Color	Q'ty Per Set (piece)	SPQ (set)	Weight (kg/set)
414-3795	MC-2AC	¥3,860	¥4,170	Black	2	1	1.5

Contact us:0120-509-849 <http://www.orange-book.com/>



MC-2A-B (with arm/blue)

MC-2AC (exclusive elbow)