

Total 89 models

Unit (mm)

Model Number	Outside Diameter ϕD	Length of Cut ℓ	Shank Taper Angle $B\alpha$	Overall Length L	Shank Diameter ϕd	Suggested Retail Price ¥
CZS 4010-0150	1	1.5	16°	50	4	6,900
CZS 4010-0250		2.5		50		6,900
CZS 4011-0250	1.1	2.5	16°	50	4	8,630
CZS 4012-0250	1.2	2.5	16°	50	4	8,630
CZS 4013-0300	1.3	3	16°	50	4	8,630
CZS 4014-0300	1.4	3	16°	50	4	8,630
CZS 4015-0225	1.5	2.25	16°	50	4	6,900
CZS 4015-0400		4		50		6,900
CZS 4016-0400	1.6	4	16°	50	4	8,630
CZS 4017-0400	1.7	4	16°	50	4	8,630
CZS 4018-0400	1.8	4	16°	50	4	8,630
CZS 4019-0400	1.9	4	16°	50	4	8,630
CZS 4020-0300	2	3	16°	50	4	6,300
CZS 4020-0600		6		50		6,300
CZS 4021-0600	2.1	6	16°	50	4	7,870
CZS 4022-0600	2.2	6	16°	50	4	7,870
CZS 4023-0600	2.3	6	16°	50	4	7,870
CZS 4024-0600	2.4	6	16°	50	4	7,870
CZS 4025-0375	2.5	3.75	16°	50	4	6,300
CZS 4025-0800		8		50		6,300
CZS 4026-0800	2.6	8	16°	50	4	7,870
CZS 4027-0800	2.7	8	16°	50	4	7,870
CZS 4028-0800	2.8	8	16°	50	4	7,870
CZS 4029-0800	2.9	8	16°	50	4	7,870
CZS 4030-0450	3	4.5	16°	60	6	7,500
CZS 4030-0800		8		60		7,500
CZS 4031-0800	3.1	8	16°	60	6	9,400
CZS 4032-0800	3.2	8	16°	60	6	9,400
CZS 4033-0800	3.3	8	16°	60	6	9,400
CZS 4034-0800	3.4	8	16°	60	6	9,400
CZS 4035-1000	3.5	10	16°	60	6	8,700
CZS 4036-1000	3.6	10	16°	60	6	9,400
CZS 4037-1000	3.7	10	16°	60	6	9,400
CZS 4038-1000	3.8	10	16°	60	6	9,400

4 Flutes

$\phi 3$ mm Shank
V Series

UDC-PCD
Series

CBN
Series

Square

Square

Long Neck
Square

Radius

Radius

Long Neck
Radius

Taper Neck
Radius

Ball / Long
Shank Ball

Ball

Long Neck
Ball

Taper Neck
Ball

Taper

Taper

Barrel

Spiral
V Cutter

Drill

Technical Data

Next Page ➡

203