

Total 21 models

Unit (mm)

Model Number	Diameter ϕD	Flute Length ℓ	Overall Length L	Shank Diameter ϕd	Suggested Retail Price ¥
UTDF 2200-080	2	8	50	4	6,500
UTDF 2250-100	2.5	10	50	4	6,500
UTDF 2300-120	3	12	60	6	6,500
UTDF 2330-132	3.3	13.2	60	6	7,000
UTDF 2400-160	4	16	60	6	7,200
UTDF 2420-168	4.2	16.8	60	6	7,500
UTDF 2500-200	5	20	60	6	7,800
UTDF 2510-204	5.1	20.4	60	6	7,800
UTDF 2600-240	6	24	60	6	8,000
UTDF 2650-130	6.5	13	70	8	9,700
UTDF 2680-272	6.8	27.2	70	8	9,700
UTDF 2700-280	7	28	80	8	9,700
UTDF 2800-320	8	32	80	8	10,500
UTDF 2850-340	8.5	34	80	10	11,500
UTDF 2860-344	8.6	34.4	80	10	11,500
UTDF 2900-360	9	36	80	10	13,500
UTDF 2950-190	9.5	19	90	10	13,500
UTDF 21000-400	10	40	90	10	13,500
UTDF 21030-412	10.3	41.2	90	12	14,000
UTDF 21100-220	11	22	100	12	15,500
UTDF 21200-480	12	48	100	12	15,500

*Contact our sales for the custom size tool.

 $\phi 3$ mm Shank
V SeriesUDC-PCD
SeriesCBN
Series

Square

Square
Long Neck
Square

Radius

Radius
Long Neck
Radius
Taper Neck
Radius

Ball

Ball / Long
Shank Ball
Long Neck
Ball
Taper Neck
Ball

Taper

Taper

Barrel

Barrel

Spiral

Spiral
V Cutter

Drill

Drill

Technical Data

Technical Data