

**D3M**

〈ピッチ：3.0mm〉

呼 称	ピッチ周長(mm)	歯数
285-D3M	285.00	95
291-D3M	291.00	97
300-D3M	300.00	100
303-D3M	303.00	101
309-D3M	309.00	103
312-D3M	312.00	104
318-D3M	318.00	106
324-D3M	324.00	108
327-D3M	327.00	109
330-D3M	330.00	110
333-D3M	333.00	111
336-D3M	336.00	112
339-D3M	339.00	113
342-D3M	342.00	114
351-D3M	351.00	117
360-D3M	360.00	120
363-D3M	363.00	121
375-D3M	375.00	125
384-D3M	384.00	128
393-D3M	393.00	131
396-D3M	396.00	132
402-D3M	402.00	134
405-D3M	405.00	135
420-D3M	420.00	140
423-D3M	423.00	141
426-D3M	426.00	142
432-D3M	432.00	144
435-D3M	435.00	145
438-D3M	438.00	146
441-D3M	441.00	147
444-D3M	444.00	148
459-D3M	459.00	153
462-D3M	462.00	154
468-D3M	468.00	156
471-D3M	471.00	157
477-D3M	477.00	159
483-D3M	483.00	161
486-D3M	486.00	162
501-D3M	501.00	167
504-D3M	504.00	168
510-D3M	510.00	170
513-D3M	513.00	171
516-D3M	516.00	172
519-D3M	519.00	173
537-D3M	537.00	179
549-D3M	549.00	183
552-D3M	552.00	184
564-D3M	564.00	188
567-D3M	567.00	189
579-D3M	579.00	193
597-D3M	597.00	199
609-D3M	609.00	203
633-D3M	633.00	211
639-D3M	639.00	213
648-D3M	648.00	216
651-D3M	651.00	217
654-D3M	654.00	218
660-D3M	660.00	220
666-D3M	666.00	222
672-D3M	672.00	224
681-D3M	681.00	227
687-D3M	687.00	229
690-D3M	690.00	230
693-D3M	693.00	231
699-D3M	699.00	233
702-D3M	702.00	234
705-D3M	705.00	235
723-D3M	723.00	241
732-D3M	732.00	244
738-D3M	738.00	246
750-D3M	750.00	250
783-D3M	783.00	261
804-D3M	804.00	268
825-D3M	825.00	275
858-D3M	858.00	286
861-D3M	861.00	287
873-D3M	873.00	291
936-D3M	936.00	312
1026-D3M	1026.00	342
1038-D3M	1038.00	346
1050-D3M	1050.00	350
1086-D3M	1086.00	362
1110-D3M	1110.00	370
1188-D3M	1188.00	396
1227-D3M	1227.00	409
1260-D3M	1260.00	420
1500-D3M	1500.00	500
1800-D3M	1800.00	600

## ■標準ベルト幅

ベルト幅(mm)
6.0
9.0
15.0

**D5M**

〈ピッチ：5.0mm〉

呼 称	ピッチ周長(mm)	歯数
375-D5M	375.00	75
385-D5M	385.00	77
400-D5M	400.00	80
405-D5M	405.00	81
410-D5M	410.00	82
420-D5M	420.00	84
450-D5M	450.00	90
465-D5M	465.00	93
475-D5M	475.00	95
500-D5M	500.00	100
520-D5M	520.00	104
550-D5M	550.00	110
560-D5M	560.00	112
565-D5M	565.00	113
575-D5M	575.00	115
580-D5M	580.00	116
600-D5M	600.00	120
615-D5M	615.00	123
625-D5M	625.00	125
635-D5M	635.00	127
640-D5M	640.00	128
645-D5M	645.00	129
670-D5M	670.00	134
695-D5M	695.00	139
710-D5M	710.00	142
720-D5M	720.00	144
740-D5M	740.00	148
770-D5M	770.00	154
775-D5M	775.00	155
800-D5M	800.00	160
810-D5M	810.00	162
830-D5M	830.00	166
845-D5M	845.00	169
860-D5M	860.00	172
870-D5M	870.00	174
890-D5M	890.00	178
900-D5M	900.00	180
920-D5M	920.00	184
930-D5M	930.00	186
940-D5M	940.00	188
950-D5M	950.00	190
965-D5M	965.00	193
975-D5M	975.00	195
1000-D5M	1000.00	200
1025-D5M	1025.00	205
1040-D5M	1040.00	208
1050-D5M	1050.00	210
1125-D5M	1125.00	225
1135-D5M	1135.00	227
1145-D5M	1145.00	229
1225-D5M	1225.00	245
1235-D5M	1235.00	247
1250-D5M	1250.00	250
1270-D5M	1270.00	254
1295-D5M	1295.00	259
1350-D5M	1350.00	270
1380-D5M	1380.00	276
1420-D5M	1420.00	284
1520-D5M	1520.00	304
1595-D5M	1595.00	319
1685-D5M	1685.00	337
1690-D5M	1690.00	338
1800-D5M	1800.00	360
1870-D5M	1870.00	374
2000-D5M	2000.00	400
2350-D5M	2350.00	470

## ■標準ベルト幅

ベルト幅(mm)
9.0
15.0
25.0

**D8M**

〈ピッチ：8.0mm〉

呼 称	ピッチ周長(mm)	歯数
424-D8M	424.00	53
480-D8M	480.00	60
560-D8M	560.00	70
584-D8M	584.00	73
600-D8M	600.00	75
640-D8M	640.00	80
680-D8M	680.00	85
720-D8M	720.00	90
760-D8M	760.00	95
800-D8M	800.00	100
840-D8M	840.00	105
856-D8M	856.00	107
880-D8M	880.00	110
896-D8M	896.00	112
920-D8M	920.00	115
960-D8M	960.00	120
1000-D8M	1000.00	125
1040-D8M	1040.00	130
1056-D8M	1056.00	132
1080-D8M	1080.00	135
1120-D8M	1120.00	140
1152-D8M	1152.00	144
1184-D8M	1184.00	148
1192-D8M	1192.00	149
1200-D8M	1200.00	150
1248-D8M	1248.00	156
1264-D8M	1264.00	158
1280-D8M	1280.00	160
1304-D8M	1304.00	163
1320-D8M	1320.00	165
1360-D8M	1360.00	170
1392-D8M	1392.00	174
1400-D8M	1400.00	175
1424-D8M	1424.00	178
1440-D8M	1440.00	180
1480-D8M	1480.00	185
1520-D8M	1520.00	190
1600-D8M	1600.00	200
1680-D8M	1680.00	210
1760-D8M	1760.00	220
1800-D8M	1800.00	225
1904-D8M	1904.00	238
1936-D8M	1936.00	242
2000-D8M	2000.00	250
2056-D8M	2056.00	257
2104-D8M	2104.00	263
2160-D8M	2160.00	270
2240-D8M	2240.00	280
2272-D8M	2272.00	284
2400-D8M	2400.00	300
2504-D8M	2504.00	313
2600-D8M	2600.00	325
2800-D8M	2800.00	350
3048-D8M	3048.00	381
3200-D8M	3200.00	400
3280-D8M	3280.00	410
3360-D8M	3360.00	420
3600-D8M	3600.00	450
3824-D8M	3824.00	478

## ■標準ベルト幅

ベルト幅(mm)
30.0
50.0
85.0

**D14M**

〈ピッチ：14.0mm〉

呼 称	ピッチ周長(mm)	歯数
1190-D14M	1190.00	85
1330-D14M	1330.00	95
1344-D14M	1344.00	96
1400-D14M	1400.00	100
1456-D14M	1456.00	104
1512-D14M	1512.00	108
1540-D14M	1540.00	110
1568-D14M	1568.00	112
1610-D14M	1610.00	115
1638-D14M	1638.00	117
1652-D14M	1652.00	118
1680-D14M	1680.00	120
1736-D14M	1736.00	124
1778-D14M	1778.00	127
1890-D14M	1890.00	135
1932-D14M	1932.00	138
1946-D14M	1946.00	139
2002-D14M	2002.00	143
2100-D14M	2100.00	150
2198-D14M	2198.00	157
2310-D14M	2310.00	165
2450-D14M	2450.00	175
2590-D14M	2590.00	185
2660-D14M	2660.00	190
2800-D14M	2800.00	200
2940-D14M	2940.00	210
3150-D14M	3150.00	225
3360-D14M	3360.00	240
3500-D14M	3500.00	250
3850-D14M	3850.00	275

## ■標準ベルト幅

ベルト幅(mm)
40.0
55.0
85.0

※ツインパワーベルトのベルト長さ許容差は、特殊公差になるため、当社までお問合わせください。