

### DXL

(ピッチ : 5.080mm)

呼 称	ピッチ周長(mm)	歯数
142DXL	360.68	71
146DXL	370.84	73
148DXL	375.92	74
150DXL	381.00	75
152DXL	386.08	76
154DXL	391.16	77
156DXL	396.24	78
158DXL	401.32	79
160DXL	406.40	80
162DXL	411.48	81
164DXL	416.56	82
166DXL	421.64	83
170DXL	431.80	85
172DXL	436.88	86
174DXL	441.96	87
176DXL	447.04	88
178DXL	452.12	89
180DXL	457.20	90
182DXL	462.28	91
184DXL	467.36	92
188DXL	477.52	94
190DXL	482.60	95
192DXL	487.68	96
194DXL	492.76	97
196DXL	497.84	98
198DXL	502.92	99
200DXL	508.00	100
202DXL	513.08	101
204DXL	518.16	102
206DXL	523.24	103
210DXL	533.40	105
212DXL	538.48	106
214DXL	543.56	107
218DXL	553.72	109
220DXL	558.80	110
224DXL	568.96	112
228DXL	579.12	114
230DXL	584.20	115
234DXL	594.36	117
240DXL	609.60	120
244DXL	619.76	122
248DXL	629.92	124
250DXL	635.00	125
258DXL	655.32	129
260DXL	660.40	130
266DXL	675.64	133
270DXL	685.80	135
276DXL	701.04	138
278DXL	706.12	139
280DXL	711.20	140

呼 称	ピッチ周長(mm)	歯数
290DXL	736.60	145
298DXL	756.92	149
300DXL	762.00	150
302DXL	767.08	151
310DXL	787.40	155
320DXL	812.80	160
322DXL	817.88	161
332DXL	843.28	166
340DXL	863.60	170
348DXL	883.92	174
352DXL	894.08	176
356DXL	904.24	178
360DXL	914.40	180
364DXL	924.56	182
372DXL	944.88	186
376DXL	955.04	188
380DXL	965.20	190
384DXL	975.36	192
386DXL	980.44	193
390DXL	990.60	195
396DXL	1005.84	198
400DXL	1016.00	200
404DXL	1026.16	202
412DXL	1046.48	206
424DXL	1076.96	212
444DXL	1127.76	222
450DXL	1143.00	225
454DXL	1153.16	227
460DXL	1168.40	230
470DXL	1193.80	235
490DXL	1244.60	245
498DXL	1264.92	249
522DXL	1325.88	261
532DXL	1351.28	266
540DXL	1371.60	270
560DXL	1422.40	280
580DXL	1473.20	290
630DXL	1600.20	315
648DXL	1645.92	324
670DXL	1701.80	335
810DXL	2057.40	405
860DXL	2184.40	430
888DXL	2255.52	444

■標準ベルト幅

呼び幅	ベルト幅(mm)
025	6.4
031	7.9
037	9.5
050	12.7

### DL

(ピッチ : 9.525mm)

呼 称	ピッチ周長(mm)	歯数
150DL	381.00	40
165DL	419.10	44
172DL	438.15	46
187DL	476.25	50
206DL	523.88	55
210DL	533.40	56
225DL	571.50	60
240DL	609.60	64
248DL	628.65	66
255DL	647.70	68
259DL	657.22	69
263DL	666.75	70
270DL	685.80	72
277DL	704.85	74
285DL	723.90	76
300DL	762.00	80
315DL	800.10	84
319DL	809.62	85
322DL	819.15	86
334DL	847.72	89
345DL	876.30	92
360DL	914.40	96
367DL	933.45	98
375DL	952.50	100
390DL	990.60	104
394DL	1000.12	105
420DL	1066.80	112
427DL	1085.85	114
450DL	1143.00	120
465DL	1181.10	124
480DL	1219.20	128
510DL	1295.40	136
525DL	1333.50	140
540DL	1371.60	144
600DL	1524.00	160
619DL	1571.62	165
720DL	1828.80	192
731DL	1857.38	195
863DL	2190.75	230
915DL	2324.10	244

■標準ベルト幅

呼び幅	ベルト幅(mm)
050	12.7
075	19.1
100	25.4
150	38.1

### DH

(ピッチ : 12.700mm)

呼 称	ピッチ周長(mm)	歯数
225DH	571.50	45
230DH	584.20	46
240DH	609.60	48
255DH	647.70	51
270DH	685.80	54
280DH	711.20	56
300DH	762.00	60
315DH	800.10	63
320DH	812.80	64
330DH	838.20	66
350DH	889.00	70
360DH	914.40	72
370DH	939.80	74
390DH	990.60	78
400DH	1016.00	80
410DH	1041.40	82
420DH	1066.80	84
430DH	1092.20	86
450DH	1143.00	90
465DH	1181.10	93
480DH	1219.20	96
490DH	1244.60	98
510DH	1295.40	102
540DH	1371.60	108
560DH	1422.40	112
570DH	1447.80	114
580DH	1473.20	116
600DH	1524.00	120
630DH	1600.20	126
640DH	1625.60	128
660DH	1676.40	132
680DH	1727.20	136
700DH	1778.00	140
750DH	1905.00	150
800DH	2032.00	160
850DH	2159.00	170
900DH	2286.00	180
950DH	2413.00	190
1000DH	2540.00	200
1100DH	2794.00	220
1120DH	2844.80	224
1130DH	2870.20	226
1250DH	3175.00	250
1345DH	3416.30	269
1400DH	3556.00	280

■標準ベルト幅

呼び幅	ベルト幅(mm)
075	19.1
100	25.4
150	38.1
200	50.8
300	76.2

特殊  
ベルト

※ツインパワーベルトのベルト長さ許容差は、特殊公差になるため、当社までお問合わせください。