

5GTプーリ寸法表

下表は、標準在庫プーリ・受注生産プーリをご検討いただく際の参考寸法です。表以外の歯数・寸法のプーリも製作いたします。当社までお問い合わせください。

単位 mm

歯数	PD	OD	C(FID)	FOD	B	H	フランジ呼称
14	22.28	21.14	16.0	26	6	12	FS(A)10026016
15	23.87	22.73	17.0	27	6	13	FS(A)10027017
16	25.46	24.32	19.0	29	6	15	FS(A)10029019
17	27.06	25.91	20.0	31	6	16	FS(A)10031020
18	28.65	27.50	22.0	32	6	18	FS(A)10032022
19	30.24	29.10	23.0	34	6	19	FS(A)10034023
20	31.83	30.69	24.0	35	8	20	FS(A)10035024
21	33.42	32.28	26.0	37	8	22	FS(A)10037026
22	35.01	33.87	27.0	39	8	22	FS(A)10039027
23	36.61	35.46	29.0	40	8	24	FS(A)10040029
24	38.20	37.05	30.0	42	8	26	FS(A)10042030
25	39.79	38.65	32.0	43	8	28	FS(A)10043032
26	41.38	40.24	33.0	45	10	28	FS(A)10045033
27	42.97	41.83	34.0	47	10	30	FS(A)10047034
28	44.56	43.42	36.0	48	10	30	FS(A)10048036
29	46.15	45.01	38.0	50	10	32	FS(A)10050038
30	47.75	46.60	39.0	51	10	32	FS(A)10051039
31	49.34	48.20	41.0	53	10	34	FS(A)10053041
32	50.93	49.79	42.0	55	10	34	FS(A)10055042
33	52.52	51.38	44.0	56	12	36	FS(A)10056044
34	54.11	52.97	46.0	58	12	36	FS(A)10058046
35	55.70	54.56	47.0	59	12	36	FS(A)10059047
36	57.30	56.15	49.0	61	12	38	FS(A)10061049
37	58.89	57.74	50.0	63	12	38	FS(A)10063050
38	60.48	59.34	52.0	64	12	38	FS(A)10064052
39	62.07	60.93	54.0	66	12	40	FS(A)10066054
40	63.66	62.52	55.0	67	12	40	FS(A)10067055
41	65.25	64.11	57.0	69	12	40	FS(A)12069057
42	66.85	65.70	58.0	71	12	42	FS(A)10071058
43	68.44	67.29	60.0	72	12	42	FS(A)12072060
44	70.03	68.89	62.0	74	12	42	FS(A)10074062
45	71.62	70.48	63.0	75	12	44	FS(A)10075063
46	73.21	72.07	65.0	77	12	44	FS(A)10077065
47	74.80	73.66	66.0	79	12	44	FS(A)12079066
48	76.39	75.25	68.0	80	12	46	FS(A)10080068
49	77.99	76.84	69.0	82	12	46	FS(A)12082069
50	79.58	78.43	71.0	83	12	46	FS(A)10083071
51	81.17	80.03	73.0	85	12	46	-
52	82.76	81.62	74.0	86	12	48	FS(A)10086074
53	84.35	83.21	76.0	88	12	48	-
54	85.94	84.80	77.0	90	12	48	FS(A)10090077
55	87.54	86.39	79.0	91	12	48	-
56	89.13	87.98	81.0	93	12	50	FS(A)10093081
57	90.72	89.58	82.0	94	12	50	-
58	92.31	91.17	84.0	96	12	50	FS(A)12096084
59	93.90	92.76	85.0	98	12	50	-
60	95.49	94.35	87.0	99	12	52	FS(A)12099087
61	97.08	95.94	89.0	101	12	52	-
62	98.68	97.53	90.0	102	12	52	FS(A)12102090
63	100.27	99.12	92.0	104	12	52	-
64	101.86	100.72	93.0	106	16	54	FS(A)12106093
65	103.45	102.31	95.0	107	16	54	-
66	105.04	103.90	96.0	109	16	54	FS(A)12109096
67	106.63	105.49	98.0	110	16	54	-
68	108.23	107.08	100.0	112	16	56	FS(A)12112100
69	109.82	108.67	101.0	114	16	56	-
70	111.41	110.27	103.0	115	16	56	-
71	113.00	111.86	104.0	117	16	56	-
72	114.59	113.45	106.0	118	16	56	FS(A)12118106
73	116.18	115.04	108.0	120	16	58	-
74	117.77	116.63	109.0	122	16	58	-
75	119.37	118.22	111.0	123	16	58	-
76	120.96	119.81	112.0	125	16	58	-
77	122.55	121.41	114.0	126	16	58	-
78	124.14	123.00	116.0	128	16	60	-
79	125.73	124.59	117.0	129	16	60	-
80	127.32	126.18	119.0	131	16	60	-
81	128.92	127.77	120.0	133	16	60	-
82	130.51	129.36	122.0	134	16	60	-

歯数	PD	OD	C(FID)	FOD	B	H	フランジ呼称
83	132.10	130.96	124.0	136	16	62	-
84	133.69	132.55	125.0	137	16	62	FS(A)12137125
85	135.28	134.14	127.0	139	16	62	-
86	136.87	135.73	128.0	141	16	62	-
87	138.46	137.32	130.0	142	16	62	-
88	140.06	138.91	132.0	144	16	64	-
89	141.65	140.50	133.0	145	16	64	-
90	143.24	142.10	135.0	147	16	64	-
91	144.83	143.69	136.0	149	16	64	-
92	146.42	145.28	138.0	150	16	64	-
93	148.01	146.87	139.0	152	16	64	-
94	149.61	148.46	141.0	153	16	66	-
95	151.20	150.05	143.0	155	16	66	-
96	152.79	151.65	144.0	157	16	66	FS(A)12157144
97	154.38	153.24	146.0	158	16	66	-
98	155.97	154.83	147.0	160	16	66	-
99	157.56	156.42	149.0	161	16	66	-
100	159.15	158.01	151.0	163	16	68	-
101	160.75	159.60	152.0	165	16	68	-
102	162.34	161.20	154.0	166	16	68	-
103	163.93	162.79	155.0	168	16	68	-
104	165.52	164.38	157.0	169	16	68	-
105	167.11	165.97	158.0	171	16	68	-
106	168.70	167.56	160.0	172	16	70	-
107	170.30	169.15	162.0	174	16	70	-
108	171.89	170.74	163.0	176	16	70	-
109	173.48	172.34	165.0	177	16	70	-
110	175.07	173.93	166.0	179	16	70	-
111	176.66	175.52	168.0	180	16	70	-
112	178.25	177.11	170.0	182	16	70	-
113	179.85	178.70	171.0	184	16	72	-
114	181.44	180.29	173.0	185	16	72	-
115	183.03	181.89	174.0	187	16	72	-
116	184.62	183.48	176.0	188	16	72	-
117	186.21	185.07	178.0	190	16	72	-
118	187.80	186.66	179.0	192	16	72	-
119	189.39	188.25	181.0	193	16	72	-
120	190.99	189.84	182.0	195	16	74	-
121	192.58	191.43	184.0	196	16	74	-
122	194.17	193.03	186.0	198	16	74	-
123	195.76	194.62	187.0	200	16	74	-
124	197.35	196.21	189.0	201	16	74	-
125	198.94	197.80	190.0	203	16	74	-
126	200.54	199.39	192.0	204	16	74	-
127	202.13	200.98	193.0	206	20	76	-
128	203.72	202.58	195.0	207	20	76	-
129	205.31	204.17	197.0	209	20	76	-
130	206.90	205.76	198.0	211	20	76	-
131	208.49	207.35	200.0	212	20	76	-
132	210.08	208.94	201.0	214	20	76	-
133	211.68	210.53	203.0	215	20	76	-
134	213.27	212.12	205.0	217	20	76	-
135	214.86	213.72	206.0	219	20	78	-
136	216.45	215.31	208.0	220	20	78	-
137	218.04	216.90	209.0	222	20	78	-
138	219.63	218.49	211.0	223	20	78	-
139	221.23	220.08	213.0	225	20	78	-
140	222.82	221.67	214.0	227	20	78	-
141	224.41	223.27	216.0	228	20	78	-
142	226.00	224.86	217.0	230	20	78	-
143	227.59	226.45	219.0	231	20	80	-
144	229.18	228.04	221.0	233	20	80	-
145	230.77	229.63	222.0	235	20	80	-
146	232.37	231.22	224.0	236	20	80	-
147	233.96	232.81	225.0	238	20	80	-
148	235.55	234.41	227.0	239	20	80	-
149	237.14	236.00	229.0	241	20	80	-
150	238.73	237.59	230.0	242	20	80	-

□ は標準在庫プーリもご用意しております。形状については、120ページをご参照ください。
標準在庫プーリのB寸法は、下穴寸法を記載しております。