

## 14Mプーリ寸法表

下表は、標準在庫プーリ・受注生産プーリをご検討いただく際の参考寸法です。表以外の歯数・寸法のプーリも製作いたします。当社までお問い合わせください。

単位 mm

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
28	124.78	121.98	106.0	25	92	-	137	FS26137106
29	129.23	126.44	111.0	25	94	-	141	FS26141111
30	133.69	130.90	115.0	25	96	-	146	FS26146115
31	138.15	135.35	120.0	25	98	-	150	FS32150120
32	142.60	139.81	123.0	25	100	-	155	FS26155123
33	147.06	144.27	128.0	25	102	-	159	FS32159128
34	151.52	148.72	132.0	25	104	-	164	FS26164132
35	155.97	153.18	137.0	30	106	-	168	FS32168137
36	160.43	157.63	140.0	30	108	-	173	FS26173140
37	164.88	162.09	144.0	30	110	-	177	FS32177144
38	169.34	166.55	149.0	30	112	-	182	FS26182149
39	173.80	171.00	153.0	30	114	-	186	FS32186153
40	178.25	175.46	158.0	30	114	-	190	FS26190158
41	182.71	179.92	162.0	30	116	-	195	FS32195162
42	187.17	184.37	167.0	30	116	-	200	FS32200167
43	191.62	188.83	171.0	30	116	-	204	FS32204171
44	196.08	193.28	176.0	30	118	-	208	FS26208176
45	200.54	197.74	180.0	30	118	-	213	FS32213180
46	204.99	202.20	185.0	30	118	-	217	FS32217185
47	209.45	206.65	189.0	30	120	-	222	FS32222189
48	213.90	211.11	194.0	30	120	172	226	FS26226194
49	218.36	215.57	198.0	30	120	176	231	FS32231198
50	222.82	220.02	203.0	30	122	181	235	FS32235203
51	227.27	224.48	207.0	30	122	185	240	FS32240207
52	231.73	228.94	211.0	30	122	189	244	FS32244211
53	236.19	233.39	216.0	30	124	194	249	FS32249216
54	240.64	237.85	220.0	30	124	198	253	FS32253220
55	245.10	242.30	225.0	30	124	203	257	FS32257225
56	249.55	246.76	229.0	30	124	207	262	FS32262229
57	254.01	251.22	234.0	40	126	212	266	FS32266234
58	258.47	255.67	238.0	40	126	216	271	FS32271238
59	262.92	260.13	242.0	40	126	220	275	FS32275242
60	267.38	264.59	247.0	40	128	225	280	FS32280247
61	271.84	269.04	252.0	40	128	230	284	FS32284252
62	276.29	273.50	256.0	40	128	234	289	FS32289256
63	280.75	277.96	261.0	40	128	239	293	FS32293261
64	285.21	282.41	265.0	40	130	243	297	FS32297265
65	289.66	286.87	269.0	40	130	247	302	FS32302269
66	294.12	291.32	274.0	40	130	252	306	FS32306274
67	298.57	295.78	278.0	40	130	256	311	FS32311278
68	303.03	300.24	283.0	50	132	261	315	FS32315283
69	307.49	304.69	287.0	50	132	265	320	FS32320287
70	311.94	309.15	291.0	50	132	269	324	FS32324291
71	316.40	313.61	296.0	50	132	274	329	FS32329296
72	320.86	318.06	301.0	50	134	279	333	FS32333301
73	325.31	322.52	305.0	50	134	283	338	FS32338305
74	329.77	326.98	309.0	50	134	287	342	FS32342309

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
75	334.23	331.43	314.0	50	134	292	346	FS32346314
76	338.68	335.89	318.0	50	136	296	351	FS32351318
77	343.14	340.34	323.0	50	136	301	355	FS32355323
78	347.59	344.80	327.0	50	136	305	360	FS32360327
79	352.05	349.26	332.0	50	136	310	364	FS32364332
80	356.51	353.71	336.0	50	138	314	369	FS32369336
81	360.96	358.17	341.0	50	138	319	373	FS32373341
82	365.42	362.63	345.0	50	138	323	378	FS32378345
83	369.88	367.08	349.0	50	138	327	382	FS32382349
84	374.33	371.54	354.0	50	140	332	387	FS32387354
85	378.79	375.99	358.0	50	140	336	391	FS32391358
86	383.25	380.45	363.0	50	140	341	395	FS32395363
87	387.70	384.91	367.0	50	140	345	400	FS32400367
88	392.16	389.36	372.0	50	142	350	404	FS32404372
89	396.61	393.82	376.0	50	142	354	409	FS32409376
90	401.07	398.28	381.0	50	142	359	413	FS32413381
91	405.53	402.73	385.0	50	142	363	418	-
92	409.98	407.19	390.0	50	144	368	422	-
93	414.44	411.65	394.0	50	144	372	427	-
94	418.90	416.10	398.0	50	144	376	431	-
95	423.35	420.56	403.0	50	144	381	436	-
96	427.81	425.01	407.0	50	146	385	440	FS32440407
97	432.26	429.47	412.0	50	146	390	445	-
98	436.72	433.93	416.0	50	146	394	449	-
99	441.18	438.38	421.0	50	146	399	453	-
100	445.63	442.84	425.0	50	148	403	458	-
101	450.09	447.30	430.0	50	148	408	462	-
102	454.55	451.75	434.0	50	148	412	467	-
103	459.00	456.21	439.0	50	148	417	471	-
104	463.46	460.67	443.0	50	150	421	476	-
105	467.92	465.12	447.0	50	150	425	480	-
106	472.37	469.58	452.0	50	150	430	485	-
107	476.83	474.03	456.0	50	150	434	489	-
108	481.28	478.49	461.0	50	152	439	494	-
109	485.74	482.95	465.0	50	152	443	498	-
110	490.20	487.40	470.0	50	152	448	502	-
111	494.65	491.86	474.0	50	152	452	507	-
112	499.11	496.32	479.0	50	154	457	511	-
113	503.57	500.77	483.0	60	154	461	516	-
114	508.02	505.23	487.0	60	154	465	520	-
115	512.48	509.68	492.0	60	154	470	525	-
116	516.94	514.14	496.0	60	156	474	529	-
117	521.39	518.60	501.0	60	156	479	534	-
118	525.85	523.05	505.0	60	156	483	538	-
119	530.30	527.51	510.0	60	156	488	543	-
120	534.76	531.97	514.0	60	158	492	547	-

□ は標準在庫プーリもご用意しております。形状については、130ページをご参照ください。  
標準在庫プーリのB寸法は、下穴寸法を記載しております。