





Bronze ball valve series


CHELIC PNEUMATIC


Model	Specification
Bronze ball valve / Double male	
	
MM11	1/8 male × 1/8 male
MM22	1/4 male × 1/4 male
MM33	3/8 male × 3/8 male
MM44	1/2 male × 1/2 male


Model	Specification
Bronze ball valve / Male hose	
	
MH20	1/4 male × 5/16 Tube
MH23	1/4 male × 3/8 Tube
MH30	3/8 male × 5/16 Tube
MH33	3/8 male × 3/8 Tube
MH40	1/2 male × 5/16 Tube
MH43	1/2 male × 3/8 Tube


Model	Port size mm	Thread size
Mini straight		
		
<small>SPT series</small>		
SPA 4 - M3	Ø 4	M3 x 0.5
SPA 4 - M5	Ø 4	M5 x 0.8
SPA 6 - M5	Ø 6	M5 x 0.8


Model	Specification
Bronze ball valve / Double female	
	
FF11	1/8 female × 1/8 female
FF22	1/4 female × 1/4 female
FF33	3/8 female × 3/8 female


Model	Specification
Bronze ball valve / Female hose	
	
FH20	1/4 Female × 5/16 Tube
FH30	3/8 Female × 5/16 Tube

Model	Port size mm	Thread size
Mini universal elbow		
		
<small>SPT series</small>		
SPT 4 - M5	Ø 4	M5 x 0.8
SPT 6 - M5	Ø 6	M5 x 0.8

Model	Specification
Plug	
	
<small>SPM series</small>	
SPM - M5	M5 X 0.8
SPM - 01	PT 1/8"
SPM - 02	PT 1/4"
SPM - 03	PT 3/8"
SPM - 04	PT 1/2"

Model	Specification
Bronze ball valve / Male & female	
	
MF22	1/4 female × 1/4 male
MF33	3/8 female × 3/8 male
MF44	1/2 female × 1/2 male

Model	Specification
Bronze ball valve / Hose & hose	
	
HH20	5/16 Tube × 5/16 Tube
HH33	3/8 Tube × 3/8 Tube

Model	Port size mm	Thread size
Mini straight		
		
<small>SPAB series</small>		
SPAB 4 - M5	Ø4	M5 × 0.8
SPAB 6 - M5	Ø6	M5 × 0.8
SPAB 6 - 01	Ø6	PT 1/8"