

三価ユニクロ 六角

六角



用途

薄鋼板 + C型钢

d	よび径
L1	全長
L2	刃先を含む完全ねじ部 (全ねじの場合はL1と同じ)
働き	使用可能な最大の厚み (下地材と締結物も含む)

■三価ユニクロ 六角

品番コード	ねじ タイプ	サイズ (mm)		適応板厚 (mm)	1箱容量 (本)	ケース入数 (箱)	単価 (円/本)	JANコード 49 03768	
		d×L1 (L2)	働き						
694130H	全ねじ	4×13 (13)	4	1.2~3.2	1000	10	4.50	37890 8	
694160H		4×16 (16)	7		1000		5.20	37891 5	
694190H		4×19 (19)	10		700		5.60	37892 2	
694250H		4×25 (25)	16		500		7.20	37893 9	
694300H		4×30 (30)	21		500		8.60	37894 6	
695160H		5×16 (16)	4		500		7.40	36191 7	
695190H		5×19 (19)	7		500		7.90	36140 5	
695250H		5×25 (25)	13		400		8.60	36141 2	
695350H		5×35 (35)	23		300		10.80	36142 9	
695400H		5×40 (40)	28		250		11.30	36308 9	
695450H		5×45 (35)	33		200		11.80	36143 6	
695500H		5×50 (35)	38		200		12.40	36844 2	
695550H	半ねじ	5×55 (35)	43	1.6~4.5	200	10	13.00	36215 0	
695650H	5×65 (40)	53	150		15.20		36334 8		
695750H	5×75 (45)	63	150		16.00		36335 5		
696190H	全ねじ	6×19 (19)	5	2.3~6.0	300	5	10.80	36144 3	
696250H		6×25 (25)	11		250		12.40	36145 0	
696350H		6×35 (35)	21		200		15.30	36146 7	
696400H		6×40 (40)	26		150		17.50	36336 2	
696450H		6×45 (35)	31		150		19.20	36147 4	
696500H		6×50 (35)	36		150		21.00	36148 1	
696600H		6×60 (35)	46		100		24.20	36149 8	
696700H		6×70 (40)	56		100		29.00	36150 4	
696800H		半ねじ	6×80 (45)		66		100	35.60	36151 1
696900H			6×90 (50)		76		80	38.00	36152 8
696105H			6×105 (60)		91		150	40.00	36153 5
696115H		6×115 (65)	101		150		46.00	36154 2	
696135H	6×135 (65)	121	150	53.00	36892 3				
696150H	6×150 (65)	136	150	68.00	36156 6				
69545ZH	全ねじ	5×45 (45)	33	1.6~4.5	200	10	11.80	36309 6	
69555ZH		5×55 (55)	43		200		13.00	36310 2	
69645ZH		6×45 (45)	31		150		19.20	36311 9	
69650ZH		6×50 (50)	36		150		21.00	36259 4	
69660ZH		6×60 (60)	46		100		24.20	36260 0	
69670ZH		6×70 (70)	56		100		29.00	37895 3	
69680ZH		6×80 (80)	66		100		35.60	37896 0	
69690ZH		6×90 (90)	76		80		38.00	37897 7	

※製品価格は全て参考価格(税抜き)です。製品仕様については予告なく変更する事があります。