

■ Specifications of Coil

Rated voltage	AC 100 / 200 V selective type		AC 110 / 220 V selective type	
	50 / 60 Hz common			
Nominal size	10-25A	32-65A	10-25A	32-65A
Allowable fluctuation	Rated voltage -5% to +10%			
Rated current	0.34 / 0.17 A	0.46 / 0.23 A	0.32 / 0.16 A	0.42 / 0.21 A
Starting current	1.64 / 0.82 A	1.90 / 0.95 A	1.48 / 0.74 A	1.80 / 0.90 A
Insulation class	Insulation class H			
Protective structure	Dust tight, Splash proof			
Ingress protection code	IP64 (JIS C0920)			
Insulation resistance	50 MΩ and more / 500 V megger			
Withstand voltage test	1500 V/min			
Removing lead wire	Conduit G 1/2 (CTG 16)			

* Available with a terminal box.

■ Dimensions (mm) and Weights (kg)

· DP-100, DP-100-C

Nominal size	d	L	H ₁	DP-100		DP-100-C	
				H	Weight	H	Weight
10A	Rc 3/8	70	14.5	127	1.4	174	1.7
15A	Rc 1/2	70	14.5	127	1.4	174	1.7
20A	Rc 3/4	80	17.5	131	1.5	177	1.8
25A	Rc 1	95	21.0	135	1.9	181	2.2
32A	Rc 1-1/4	110	26.0	172	3.1	218	3.4
40A	Rc 1-1/2	120	29.5	178	4.0	225	4.3
50A	Rc 2	140	36.5	187	5.6	233	5.9



· DP-100F, DP-100F-C

Nominal size	d	L	H ₁	DP-100F		DP-100F-C	
				H	Weight	H	Weight
15A	15	120	47.5	161	2.7	207	3.0
20A	20	130	50.0	164	3.2	210	3.5
25A	25	145	62.5	177	4.5	223	4.8
32A	32	160	67.5	213	6.9	260	7.2
40A	40	170	70.0	219	8.0	265	8.3
50A	50	195	77.5	228	10.5	274	10.8
65A	65	198	87.5	238	12.3	284	12.6

