

Rails for Switches and Sensors

L Configurable, Hole Position Fixed (Shape A, B and C)

■ **Features:** Rails for Sensors with L Configurable and Hole Position Fixed. More economical than Hole Position Configurable Type.

Bar Nuts **P2083**

M Material	S Surface Treatment	Part Number		
		Shape A	Shape B	Shape C
A6063S-T5	Clear Anodize	SENAF	SENBFB	SENCF

No anodizing on the tip and inner surface.
 Burrs remain on the I.D. of the mounting holes.
 No hole machining specification is required for this product.

(Shape A)
SENAF

(Shape B)
SENBFB

(Shape C)
SENCF

RoHS 10

■ **L Configurable, Hole Position Fixed** No. indicates the applicable nut size.

Bar Nuts **P2083**

Part Number	L 1mm Increment	N	N ₁	N ₂	A	B	C	D	E	d	e	Unit Price			
												SENAF		SENBFB, SENCF	
												L50-100	L101-200	L50-100	L101-200
(Shape A) SENAF	3	3.5	6.5	3.5	3.4	5.7	3.0	9	6.0	1.5	2				
(Shape B) SENBFB	4			4.5	4.5	7.2	4.0	11	8.0	2.0					
(Shape C) SENCF	5			5.5	5.5	8.2	5.5	12	9.5			3			



Part Number - **L**
SENAF3 - 100
SENCF5 - 150



Example

