

# Panel Brackets - Plastic / Panel Clamping Brackets

**Panel Brackets - Plastic**

**HCBR5** (Light Gray)  
**HCBRB5** (Black)

**HCBR6** (Light Gray)  
**HCBRB6** (Black)  
**HCBRB6S** (Black)

**HCBR8** (Light Gray)  
**HCBRB8** (Black)

**HCBR8-45** (Light Gray)  
**HCBRB8-45** (Black)

Ⓜ M5 insert nut is included inside. Use M5 screw with length 15 to attach panels.

**Example**

Since Plastic Type HCBR5 has an eccentric T-shaped stopping part, it can be used for both panels with thickness 5mm and 3mm.

**Plastic Type Mounting Method**  
Easy installation by inserting the T-shaped stopping part into the slot and turning 90°. Use mounting screws with L dimension 15 for plastic types.

Part Number		Mass	A	Difference between the Extrusion Side and Attachment Face	Unit Price 1 ~ 9 pc(s).	Volume Discount Rate 10
Type	No.					
HCBR HCBRB	5	4.3	12	3 or 5		
	6	6.8	20	5		
	6S	6.0	24	3		
	8	10.9	30	5		
	8-45*	13.2	35	5		

Ordering Example

Part Number  
**HCBR6**

\* Select No. 8 for 45 Square Light type (HFSL8-45) series.

**Panel Clamping Brackets**

**HCBS5**

**HCBS6**

**HCBS8**

Ⓜ Material: Polyamide

Ⓜ HCBS8 is commonly used for 8 Series and 8-45 Series. Ⓜ Panel thickness is adjustable by moving P part.

Part Number		Mass	P Applicable Panel Thickness	Unit Price 1 ~ 9 pc(s).	Volume Discount Rate 10
Type	No.				
HCBS	5	2.6	3~5		
	6	3.9			
	8	6.3			

- How to Mount Panel Clamps**
- ① Connection with Extrusion  
Easy installation by inserting the T-shaped stopping part into the slot and turning 90°.
  - ② Connection with Panel  
As shown on the right, insert a panel into P part and push the moving part against the panel. Hole machining on the panel is not necessary.

Ordering Example

Part Number  
**HCBS8**

**Example**