

# High Pressure Screw Fittings

Equal Dia. / Reducing

**Sockets**

Type	Material
SGPPSH	S25C
SUTPSH	SUS304

RcHS10

**Hex Sockets**

Type	Material
SGPSH	S25C

RcHS10

**Elbows**

Type	Material
SGPPEH	S25C
SUPESH	SUS304

RcHS10

**45° Elbows**

Type	Material
SGPPEH	S25C
SUTHEH	SUS304

RcHS10

**Male/Female Elbows**

Type	Material
SGPELH	S25C
SUTELH	SUS304

RcHS10

**Tees**

Type	Material
SGPPTH	S25C
SUTPTH	SUS304

RcHS10

**Plugs**

Type	Material
SGPPPJ	S25C
SUPPPJ	SUS304

RcHS10

Part Number	Type	No.	SGPPSH		SUTPSH		SGPPSH		SUTPSH	
			Rc (PT)	(D)	(L)	(D)	(L)	Unit Price	Volume Discount Rate	Unit Price
SGPPSH	6A	1/8	19	22	19	26				
	8A	1/4	22	25	22	28				
	10A	3/8	28	28	25	33				
	15A	1/2	32	32	32	37				
	20A	3/4	38	38	38	42				
SUTPSH	25A	1	46	45	45	45				
	32A	1 1/4	58	50	55	52				
	40A	1 1/2	63	55	65	56				
	50A	2	76	60	75	66				

For orders larger than indicated quantity, please check with WOS.

Part Number	Type	No.	Rc (PT)	B	(ℓ)	(D)	(L)	Unit Price		Volume Discount Rate	
								1 ~ 4 pc(s).	5-20 pcs.	1 ~ 4 pc(s).	5-20 pcs.
SGPSH	8A	1/4	22	8.5	22	28					
	10A	3/8	27	8.5	27	33					
	15A	1/2	32	9	32	37					
	20A	3/4	38	11	38	42					
	25A	1	46	12	46	45					
	32A	1 1/4	58	14	55	52					

For orders larger than indicated quantity, please check with WOS.

Part Number	Type	No.	Rc (PT)	SGPPEH		SUPESH		SGPPEH		SUPESH	
				(D)	(L)	(D)	(L)	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SGPPEH	6A	1/8	23	21.6	23	21					
	8A	1/4	23	21.6	23	21					
	10A	3/8	27	25.5	27	25					
	15A	1/2	34	28.9	34	29					
	20A	3/4	39	33.1	39	34					
SUPESH	25A	1	47	38.2	47	38					
	32A	1 1/4	56	44.6	57	45					
	40A	1 1/2	63	51.1	63	51					
	50A	2	76	58.0	77	61					

For orders larger than indicated quantity, please check with WOS.

Part Number	Type	No.	Rc (PT)	SGPHEH		SUTHEH		SGPHEH		SUTHEH	
				(D)	(L)	(D)	(L)	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SGPHEH	8A	1/4	23	18.4	23	18.4					
	10A	3/8	27	18.9	27	18.9					
	15A	1/2	34	24.1	34	24.1					
	20A	3/4	39	26.7	39	26.7					
	25A	1	47	30.3	47	30.3					
SUTHEH	32A	1 1/4	56	35.5	56	35.5					
	40A	1 1/2	63	39.6	63	39.6					
	50A	2	76	46.4	76	46.4					

For orders larger than indicated quantity, please check with WOS.

Part Number	Type	No.	R (PT)	SGPELH			SUTELH			SGPELH		SUTELH	
				(D)	(L1)	(L2)	A	B	(D)	(L1)	(L2)	A	B
SGPELH	8A	1/4	24	30	41	21	27	25	32.5	45	22	32	
	10A	3/8	24	35	41	25	28	33	39.5	55	25	38	
	15A	1/2	32	41	51	29	35	38	44.5	61	28	41	
	20A	3/4	36	47	59	33	40	46	55.5	72	35	48	
	25A	1	46	57	74	38	48	56	70.5	86	44	57	

For orders larger than indicated quantity, please check with WOS.

Part Number	Type	No.	Rc (PT)	SGPPTH		SUTPTH		SGPPTH		SUTPTH	
				(D)	(L)	(D)	(L)	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SGPPTH	8A	1/4	23	21.6	23	21.6					
	10A	3/8	27	25.5	27	25.5					
	15A	1/2	34	28.9	34	28.9					
	20A	3/4	39	33.1	39	33.1					
	25A	1	47	38.2	47	38.2					
SUTPTH	32A	1 1/4	56	44.6	56	45.0					
	40A	1 1/2	63	51.1	63	50.8					
	50A	2	76	58.0	76	60.1					

For orders larger than indicated quantity, please check with WOS.

Part Number	Type	No.	R (PT)	SGPPPJ			SUPPPJ			SGPPPJ		SUPPPJ	
				(L)	(T)	(H)	(L)	(T)	(H)	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SGPPPJ	8A	1/4	11	9	11	7	9						
	10A	3/8	12	10	12	12	9	12					
	15A	1/2	15	11	14	15	10	14					
	20A	3/4	17	12	17	17	11	17					
	25A	1	19	13	19	20	12	21					
SUPPPJ	32A	1 1/4	22	14	23	22	13	23					
	40A	1 1/2	22	15	26	22	14	28					
	50A	2	26	16	32	26	15	33					

For orders larger than indicated quantity, please check with WOS.