

Open-Ended Hose Fittings

Type: **HOSSH** Material: Brass

RoHS 10

Part Number	Applicable Hose	D	d	B1	B2	G (PF)	La	L	Unit Price	Volume Discount Rate
Type	No.	Nominal I.D.							1~4 pc(s).	5~10
HOSSH (Brass)	61	6	7	4	14	16	1/4	26	89	
	628		8	4.5	14	16	1/4	26	89	
	629		9	5	14	16	1/4	26	89	
	92	9	10.5	7	17	19	3/8	27	91	
	123	12	14	10	22	24	1/2	31	112	
	153	15	16	11.5	22	24	1/2	31	112	
196	19	20.5	15	27	30	3/4	35	120		

For orders larger than indicated quantity, please check with WOS.

Hose Barbs, Straight

Type: **HOSHS** Material: Brass

RoHS 10

Part Number	Applicable Hose	D	d	A	Unit Price	Volume Discount Rate
Type	No.	Nominal I.D.			1~4 pc(s).	5~10
HOSHS (Brass)	628	6	8	4.5	34	
	629		9	5	34	
	92	9	10.5	7	36	
	123	12	14	10	42	
	153	15	16	11.5	42	
196	19	20.5	15	46		

Fitting applicable for HOSJN and HOSSH only.

For orders larger than indicated quantity, please check with WOS.

Swaging Sleeve Nuts for Hoses

Type: **HOSHJN** Material: Brass

RoHS 10

Part Number	Main Body	Applicable	G (PF)	D	B	A	Unit Price	Volume Discount Rate
Type	No.	No.					1~4 pc(s).	5~10
HOSHJN (Brass)	2	62 63 628 629	1/4	9.5	16	13		
	3	92 93 94	3/8	11	19	14		
	4	123 124 126 153 154	1/2	16.5	24	16		
	6	194 196	3/4	21.5	30	17.5		

Fitting applicable for HOSJN and HOSSH only.

For orders larger than indicated quantity, please check with WOS.

Elbow Hose Nipples

Type: **HOSJE** Material: Brass

RoHS 10

Part Number	Applicable Hose	T	F	D	(L1)	(L2)	Unit Price	Volume Discount Rate
Type	No.	R (PT)	G (PF)				1~9 pc(s).	10~30
HOSJE (Brass)	61	6	1/8	1/8	6.5	39	20	
	82	8	1/4	1/4	8	48.5	25	
	93	9	3/8	3/8	10.0	56	28	
	124	12	1/2	1/2	14.0	72	34	

For orders larger than indicated quantity, please check with WOS.

45° Elbow Hose Nipples

Type: **HOSJH** Material: Brass

RoHS 10

Part Number	Applicable Hose	T	F	D	(L1)	(L2)	Unit Price	Volume Discount Rate
Type	No.	R (PT)	G (PF)				1~9 pc(s).	10~30
HOSJH (Brass)	61	6	1/8	1/8	6.5	39	20	
	82	8	1/4	1/4	8	48.5	25	
	93	9	3/8	3/8	10.0	56	28	
	124	12	1/2	1/2	14.0	72	34	

For orders larger than indicated quantity, please check with WOS.

Branch Tees

Type: **HOSJT** Material: Brass

RoHS 10

Part Number	Applicable Hose	T	F	D	(L1)	(L)	Unit Price	Volume Discount Rate
Type	No.	Rc (PT)	G (PF)				1~9 pc(s).	10~30
HOSJT (Brass)	61	6	1/8	1/8	6.5	39	78	
	82	8	1/4	1/4	8	48.5	97	
	93	9	3/8	3/8	10.0	56	112	
	124	12	1/2	1/2	14.0	72	144	

For orders larger than indicated quantity, please check with WOS.

Ordering Example

Part Number: **HOSJE61**

Specifications	Applicable Fluids	Water, Air, Oil
	Operating Temperature Range	-20~150°C (No Freezing)
	Max. Operating Pressure	3.5MPa