

Food Grade Hose

For Food Processing Machines and Facilities

EIGHTLOCK® S/B EIGHTNIPPLE S Spring Guards



E-KYS

KY SUNFOODS HOSE


- E-KYS is made of non-vinyl chloride materials which are suitable for transporting foods and beverages. Also, E-KYS is able to transfer fats and fatty oil.
- Non-oil materials, which do not contain any plasticizer, are used and minimize odious smell peculiar to resins.
- E-KYS is an eco-friendly hose, which restrains the production of harmful gas, even though it is burned out.
- Olefinic resin, which is suitable for fats, fatty oils, and fatty foods, is used in the inner layer of the hose.
- E-KYS conforms to the Food Sanitation Law No.201 (No. 201 of the Ministry of Health and Welfare for Food Sanitation) (Conformity to N-Heptane).

EIGHTRON®

Non-PVC



RoHS Compliant



Model Number	I.D. × O.D.		Working Pressure (MPa)		Minimum Bend Radius (20°C)	Temperature Range	Standard Length	Weight	Package Type	Color
	mm		at 20°C	at 65°C	mm	°C	m	g/m		
E-KYS-6	6 × 11				45		100	65		
E-KYS-8	8 × 13.5				60		100	90		
E-KYS-9	9 × 15				65		100	110		
E-KYS-10	10 × 16		0 ~ 0.8	0 ~ 0.4	70		100	120		
E-KYS-12	12 × 18				85		100	140		
E-KYS-15	15 × 22				105	0 ~ 65	50	205	Film Wrapping	Natural
E-KYS-19	19 × 26				135		50	245		
E-KYS-25	25 × 33		0 ~ 0.5	0 ~ 0.3	175		50	360		
E-KYS-32	32 × 41		0 ~ 0.4	0 ~ 0.2	225		50	510		
E-KYS-38	38 × 48				265		50	640		
E-KYS-50	50 × 62		0 ~ 0.3	0 ~ 0.2	400		50	1,000		

EIGHTNIPPLE S Spring Guards



E-OHB

KY SOFT BRAID HOSE


- E-OHB hose is suitable for use in liquor and brewing, because it contains low levels of elution and is handled easily.
- Non-oil materials, which do not contain plasticizer, are used and can minimize odious smell peculiar to resins.
- E-OHB hose is an eco-friendly hose, which restrains the production of harmful gas, even though it is burned out.
- Special Olefinic Resin, which is suitable for fats and fatty oils, is used in the inner layer of the hose.
- E-OHB hose conforms to the Food Sanitation Law No.201 (No. 201 of the Ministry of Health and Welfare for Food Sanitation) (Conformity to N-Heptane).

EIGHTRON®

Non-PVC



RoHS Compliant



Model Number	I.D. × O.D.		Working Pressure (MPa)		Minimum Bend Radius (20°C)	Temperature Range	Standard Length	Weight	Package Type	Color
	mm		at 20°C	at 70°C	mm	°C	m	g/m		
E-OHB-25	25 × 33		0 ~ 0.5	0 ~ 0.2	175		50	360		
E-OHB-38	38 × 49		0 ~ 0.5	0 ~ 0.2	265	-10 ~ 70	50	700	Film Wrapping	Natural
E-OHB-50	50 × 63		0 ~ 0.4	0 ~ 0.15	350		50	1,070		