

# PSS-22

ピン (□) 2.00mmピッチ ストレート (2列)

●ピン ●Pin ●排針



段重ね固定型

## 仕様

- ・電流量 / 1A
- ・絶縁抵抗 / 5000MΩ MIN (DC 500V)
- ・接触抵抗 / 20mΩ MAX (DC 100mA)
- ・動作温度範囲 / -40℃ ~ +105℃
- ・RoHS対応製品

## 材質

- 樹脂部
  - ・材質 / ナイロン
  - ・色 / 黒
  - ・熱変形温度 / 1.80MPa...290℃
  - ・燃焼性 / UL94V-0 (材料)
- コンタクト
  - ・材質 / 黄銅
  - ・処理 / Ni下地 金フラッシュ



	PSS-220153 (H=1.5)	PSS-220203 (H=2)	PSS-220403 (H=4)	PSS-220503 (H=5)	PSS-220603 (H=6)
--	--------------------	------------------	------------------	------------------	------------------

ピン数	品番	品番	品番	品番	品番
4	PSS-220153-02	PSS-220203-02	PSS-220403-02	PSS-220503-02	PSS-220603-02
6	PSS-220153-03	PSS-220203-03	PSS-220403-03	PSS-220503-03	PSS-220603-03
8	PSS-220153-04	PSS-220203-04	PSS-220403-04	PSS-220503-04	PSS-220603-04
10	PSS-220153-05	PSS-220203-05	PSS-220403-05	PSS-220503-05	PSS-220603-05
12	PSS-220153-06	PSS-220203-06	PSS-220403-06	PSS-220503-06	PSS-220603-06
14	PSS-220153-07	PSS-220203-07	PSS-220403-07	PSS-220503-07	PSS-220603-07
16	PSS-220153-08	PSS-220203-08	PSS-220403-08	PSS-220503-08	PSS-220603-08
18	PSS-220153-09	PSS-220203-09	PSS-220403-09	PSS-220503-09	PSS-220603-09
20	PSS-220153-10	PSS-220203-10	PSS-220403-10	PSS-220503-10	PSS-220603-10
22	PSS-220153-11	PSS-220203-11	PSS-220403-11	PSS-220503-11	PSS-220603-11
24	PSS-220153-12	PSS-220203-12	PSS-220403-12	PSS-220503-12	PSS-220603-12
26	PSS-220153-13	PSS-220203-13	PSS-220403-13	PSS-220503-13	PSS-220603-13
28	PSS-220153-14	PSS-220203-14	PSS-220403-14	PSS-220503-14	PSS-220603-14
30	PSS-220153-15	PSS-220203-15	PSS-220403-15	PSS-220503-15	PSS-220603-15
32	PSS-220153-16	PSS-220203-16	PSS-220403-16	PSS-220503-16	PSS-220603-16
34	PSS-220153-17	PSS-220203-17	PSS-220403-17	PSS-220503-17	PSS-220603-17
36	PSS-220153-18	PSS-220203-18	PSS-220403-18	PSS-220503-18	PSS-220603-18
38	PSS-220153-19	PSS-220203-19	PSS-220403-19	PSS-220503-19	PSS-220603-19
40	PSS-220153-20	PSS-220203-20	PSS-220403-20	PSS-220503-20	PSS-220603-20
42	PSS-220153-21	PSS-220203-21	PSS-220403-21	PSS-220503-21	PSS-220603-21
44	PSS-220153-22	PSS-220203-22	PSS-220403-22	PSS-220503-22	PSS-220603-22
46	PSS-220153-23	PSS-220203-23	PSS-220403-23	PSS-220503-23	PSS-220603-23
48	PSS-220153-24	PSS-220203-24	PSS-220403-24	PSS-220503-24	PSS-220603-24
50	PSS-220153-25	PSS-220203-25	PSS-220403-25	PSS-220503-25	PSS-220603-25
52	PSS-220153-26	PSS-220203-26	PSS-220403-26	PSS-220503-26	PSS-220603-26
54	PSS-220153-27	PSS-220203-27	PSS-220403-27	PSS-220503-27	PSS-220603-27
56	PSS-220153-28	PSS-220203-28	PSS-220403-28	PSS-220503-28	PSS-220603-28
58	PSS-220153-29	PSS-220203-29	PSS-220403-29	PSS-220503-29	PSS-220603-29
60	PSS-220153-30	PSS-220203-30	PSS-220403-30	PSS-220503-30	PSS-220603-30
62	PSS-220153-31	PSS-220203-31	PSS-220403-31	PSS-220503-31	PSS-220603-31
64	PSS-220153-32	PSS-220203-32	PSS-220403-32	PSS-220503-32	PSS-220603-32
66	PSS-220153-33	PSS-220203-33	PSS-220403-33	PSS-220503-33	PSS-220603-33
68	PSS-220153-34	PSS-220203-34	PSS-220403-34	PSS-220503-34	PSS-220603-34
70	PSS-220153-35	PSS-220203-35	PSS-220403-35	PSS-220503-35	PSS-220603-35
72	PSS-220153-36	PSS-220203-36	PSS-220403-36	PSS-220503-36	PSS-220603-36
74	PSS-220153-37	PSS-220203-37	PSS-220403-37	PSS-220503-37	PSS-220603-37
76	PSS-220153-38	PSS-220203-38	PSS-220403-38	PSS-220503-38	PSS-220603-38
78	PSS-220153-39	PSS-220203-39	PSS-220403-39	PSS-220503-39	PSS-220603-39
80	PSS-220153-40	PSS-220203-40	PSS-220403-40	PSS-220503-40	PSS-220603-40

ご注文個数 (~20Pin迄) 50個 ~、(22Pin~) 10個 ~