


ERU-A


●ステンレス全ネジ (精密ロングネジ) ●SUS303 threaded rod ●不锈钢全螺丝 (精密长螺丝)

仕様

- ・材質 / ステンレス鋼 (SUS303)
- ・処理 / 脱脂
- ・ネジゲージ / 2級
- ・RoHS対応製品




ERU-300A (M=3 ピッチ0.5)		L	品番	L	品番	L	品番
		10	ERU-310A	72	ERU-372A	170	ERU-3170A
		12	ERU-312A	75	ERU-375A	175	ERU-3175A
		15	ERU-315A	78	ERU-378A	180	ERU-3180A
		18	ERU-318A	80	ERU-380A	185	ERU-3185A
		20	ERU-320A	82	ERU-382A	190	ERU-3190A
		22	ERU-322A	85	ERU-385A	195	ERU-3195A
		25	ERU-325A	88	ERU-388A	200	ERU-3200A
		28	ERU-328A	90	ERU-390A	205	ERU-3205A
		30	ERU-330A	92	ERU-392A	210	ERU-3210A
		32	ERU-332A	95	ERU-395A	215	ERU-3215A
		35	ERU-335A	98	ERU-398A	220	ERU-3220A
		38	ERU-338A	100	ERU-3100A	225	ERU-3225A
		40	ERU-340A	105	ERU-3105A	230	ERU-3230A
		42	ERU-342A	110	ERU-3110A	235	ERU-3235A
		45	ERU-345A	115	ERU-3115A	240	ERU-3240A
		48	ERU-348A	120	ERU-3120A	245	ERU-3245A
		50	ERU-350A	125	ERU-3125A	250	ERU-3250A
		52	ERU-352A	130	ERU-3130A	255	ERU-3255A
		55	ERU-355A	135	ERU-3135A	260	ERU-3260A
		58	ERU-358A	140	ERU-3140A	265	ERU-3265A
		60	ERU-360A	145	ERU-3145A	270	ERU-3270A
		62	ERU-362A	150	ERU-3150A	275	ERU-3275A
		65	ERU-365A	155	ERU-3155A	280	ERU-3280A
		68	ERU-368A	160	ERU-3160A		
		70	ERU-370A	165	ERU-3165A		



Lの公差 L=100迄±0.3 L=105より±0.5

ご注文個数 10個～

ERU-400A (M=4 ピッチ0.7)		L	品番	L	品番	L	品番
		15	ERU-415A	78	ERU-478A	180	ERU-4180A
		18	ERU-418A	80	ERU-480A	185	ERU-4185A
		20	ERU-420A	82	ERU-482A	190	ERU-4190A
		22	ERU-422A	85	ERU-485A	195	ERU-4195A
		25	ERU-425A	88	ERU-488A	200	ERU-4200A
		28	ERU-428A	90	ERU-490A	205	ERU-4205A
		30	ERU-430A	92	ERU-492A	210	ERU-4210A
		32	ERU-432A	95	ERU-495A	215	ERU-4215A
		35	ERU-435A	98	ERU-498A	220	ERU-4220A
		38	ERU-438A	100	ERU-4100A	225	ERU-4225A
		40	ERU-440A	105	ERU-4105A	230	ERU-4230A
		42	ERU-442A	110	ERU-4110A	235	ERU-4235A
		45	ERU-445A	115	ERU-4115A	240	ERU-4240A
		48	ERU-448A	120	ERU-4120A	245	ERU-4245A
		50	ERU-450A	125	ERU-4125A	250	ERU-4250A
		52	ERU-452A	130	ERU-4130A	255	ERU-4255A
		55	ERU-455A	135	ERU-4135A	260	ERU-4260A
		58	ERU-458A	140	ERU-4140A	265	ERU-4265A
		60	ERU-460A	145	ERU-4145A	270	ERU-4270A
		62	ERU-462A	150	ERU-4150A	275	ERU-4275A
		65	ERU-465A	155	ERU-4155A	280	ERU-4280A
		68	ERU-468A	160	ERU-4160A		
		70	ERU-470A	165	ERU-4165A		
		72	ERU-472A	170	ERU-4170A		
		75	ERU-475A	175	ERU-4175A		



Lの公差 L=100迄±0.3 L=105より±0.5

ご注文個数 10個～